



イーサネット対応HIGH SPEED HDMIマイクロケーブル 4K/30Hz・フルHD対応のデジカメやタブレットに。ブラック・1m。

KM-HD23-10K

イーサネット対応ハイスピードHDMIマイクロケーブル（ブラック・1m）

JANコード 4969887766101



仕様

カラー	ブラック
ケーブル長	1m
ケーブル直径	約3.2mm
重量	約23g
コネクタ	HDMIマイクロプラグーHDMIプラグ（HDMIタイプDーHDMIタイプA）
HDMI規格	HIGH SPEED with ETHERNET（HDMI規格認証品）
線材規格	UL20276
被覆材料	PVC樹脂

特注不可

少量からの特注は、お受けすることができません。

数量によっては可能な場合がありますので、詳しくはサンワサプライ営業までお問い合わせください。

特長

解像度3840×2160ピクセルの映像に対応しています。（フルHD解像度は1920×1080）

HDMIイーサネットチャンネル（HEC）に対応しており、対応した機器と機器がイーサネット・ネットワークでつながります。

オーディオリターンチャンネル（ARC）に対応しているので、テレビ側から音声信号をAVアンプなどに伝送可能です。

3D映像に対応しており、対応した機器を接続することでフルHD 3D映像をお楽しみいただけます。

Deepカラー対応色深度が24ビット（フルカラー）を超え、30/36/48bitまで対応しています。

高音質デジタル音声信号（マルチチャンネルサラウンド）対応です。

※対応したソフトや機器が必要です。

対応情報

対応機種	(出力側)
	マイクロHDMI出力端子 (HDMIタイプDメス) を搭載した機器 (タブレット・デジカメなど)
	または HDMI出力端子 (HDMIタイプAメス) を搭載したブルーレイ・HDD・DVDレコーダー、パソコン、ゲーム機など
	(入力側)
	HDMI入力端子 (HDMIタイプAメス) を搭載したディスプレイ、プロジェクター、液晶テレビなど
	または マイクロHDMI入力端子 (HDMIタイプDメス) を搭載したディスプレイ、プロジェクター、液晶テレビなど

High-speed HDMI micro cable with Ethernet for 4K/30Hz and Full HD digital cameras and tablets. Black, 1m. KM-HD23-10K

Specification

- Color : black
- Cable length : 1m
- Cable diameter : Approximately 3.2 mm
- Weight Approximately : 23g
- Connector : HDMI micro plug to HDMI plug (HDMI Type D to HDMI Type A)
- HDMI standard : HIGH SPEED with ETHERNET (HDMI standard certified product)
- Wire standard : UL20276
- Coating materials : PVC resin

We cannot accept small quantities of special orders. Depending on the quantity, it may be possible, so please contact Sanwa Supply Sales for details.

Features

- Supports video resolution of 3840 x 2160 pixels (Full HD resolution is 1920 x 1080).
- It supports HDMI Ethernet Channel (HEC), allowing compatible devices to be connected via an Ethernet network.
- It supports Audio Return Channel (ARC), so audio signals can be transmitted from the TV to an AV amplifier or other device.
- It supports 3D images, and by connecting compatible devices you can enjoy full HD 3D images.
- Deep color support: Color depth exceeds 24-bit (full color) and supports up to 30/36/48-bit.
- Supports high-quality digital audio signals (multi-channel surround).
*Compatible software and equipment are required.