



## MIC25-10MM-3/8"-A

Ruland MIC25-10MM-3/8"-A, 10mm x 10mm Single Beam Coupling, Aluminum, Clamp Style, 0.984" (25.0mm) OD, 1.181" (30.0mm) Length



### Description

Ruland MIC25-10MM-3/8"-A is a single beam coupling with 10mm x 0.3750", 0.984" (25.0mm) OD, and 1.181" (30.0mm) length. It is machined from a single piece of material and feature one long continuous spiral cut. This gives it higher misalignment capabilities than comparably sized multiple beam couplings. MIC25-10MM-3/8"-A is zero-backlash making it well suited for applications such as encoders that require high positioning accuracy. MIC-series couplings have purely metric outer diameter and length dimensions and fit in a smaller envelope than the ICR-series. All hardware is metric and tests beyond DIN 912 12.9 standards for maximum torque capabilities. MIC25-10MM-3/8"-A is made from 7075 aluminum for lightweight and low inertia. It is machined from bar stock that is sourced exclusively from North American mills and RoHS3, REACH, and Conflict Minerals compliant. MIC25-10MM-3/8"-A is manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

### Product Specifications

|                                     |   |                                       |   |
|-------------------------------------|---|---------------------------------------|---|
| <b>Bore (B1)</b>                    | 10 mm                                     | <b>Small Bore (B2)</b>                | 0.3750 in                                     |
| <b>B1 Max Shaft Penetration</b>     | 0.576 in (14.6 mm)                        | <b>B2 Max Shaft Penetration</b>       | 0.576 in (14.6 mm)                            |
| <b>Outer Diameter (OD)</b>          | 0.984 in (25.0 mm)                        | <b>Bore Tolerance</b>                 | +0.001 in / -0.000 in (+0.025 mm / -0.000 mm) |
| <b>Length (L)</b>                   | 1.181 in (30.0 mm)                        | <b>Recommended Shaft Tolerance</b>    | +0.0000 / -0.0005 " (+0.000 / -0.013 mm)      |
| <b>Cap Screw</b>                    | M3  | <b>Screw Material</b>                 | Alloy Steel                                   |
| <b>Hex Wrench Size</b>              | 2.5 mm                                    | <b>Screw Finish</b>                   | Black Oxide                                   |
| <b>Seating Torque</b>               | 2.1 Nm                                    | <b>Number of Screws</b>               | 2 ea  |
| <b>Dynamic Torque Reversing</b>     | 0.85 Nm                                   | <b>Angular Misalignment</b>           | 5.0°  |
| <b>Dynamic Torque Non-Reversing</b> | 1.70 Nm                                   | <b>Parallel Misalignment</b>          | 0.25 mm                                       |
| <b>Static Torque</b>                | 3.39 Nm                                   | <b>Axial Motion</b>                   | 0.25 mm                                       |
| <b>Torsional Stiffness</b>          | 3.58 Deg/Nm                               | <b>Moment of Inertia</b>              | 2.792 x10 <sup>-6</sup> kg-m <sup>2</sup>     |
| <b>Maximum Speed</b>                | 6,000 RPM                                 | <b>Full Bearing Support Required?</b> | Yes   |
| <b>Zero-Backlash?</b>               | Yes                                       | <b>Recommended Hex Key</b>            | <a href="#">Metric Hex Keys</a>               |
| <b>Material Specification</b>       | 7075-T651 Extruded and Drawn Aluminum Bar | <b>Temperature</b>                    | -40°F to 225°F (-40°C to 107°C)               |
| <b>Finish Specification</b>         | Bright, No Plating                        | <b>Manufacturer</b>                   | Ruland Manufacturing                          |
| <b>Country of Origin</b>            | USA                                       | <b>Weight (lbs)</b>                   | 0.067910                                      |
| <b>UPC</b>                          | 63452943728                               | <b>Tariff Code</b>                    | 8483.60.8000                                  |
| <b>UNSPC</b>                        | 31163003                                  |                                       |   |

**Note 1** Torque ratings are at maximum misalignment.

**Note 2** Performance ratings are for guidance only. The user must determine suitability for a particular application.

**Note 3** Torque ratings for the couplings are based on the physical limitations/failure point of the machined beams. Under normal/typical conditions the hubs are capable of holding up to the rated torque of the machined beams. In some cases especially when the smallest standard bores are used or where shafts are undersized slippage on the shaft is possible below the rated torque of the machined beams. Please consult technical

