


Door Opening Detector, 2 m, 4-core

Art. no. MK4000

Page 1 of 1



- Magnetic contact for installation and assembly
- NC switching contact
- 2 m cable / 4-wire

The door opening detector is a magnetic contact for protecting large (garage) doors. Unauthorised opening is detected and reported to the alarm panel. The door opening detector is mounted chiefly on roll-up, sliding, and up-and-over doors. The detector consists of a magnetic contact (reed) and a magnet. These are fitted parallel to each other. The electric circuit of this NC opening detector is normally closed (NC). If the distance between reed and magnet increases, the circuit is broken and an alarm reported. The detector is tamper-protected. The best installation location is in the middle of the entrance. The magnetic contact is mounted on the ground and the magnet on the inside of the door at a distance of about 20 mm. The door opening detector is perfectly suited for surface-fitting. It is absolutely water and dust-proof (IP 68). Its extremely robust aluminium housing protects it from damage even when driven over. The door opening detector is VdS B certified.

Technical Data:

Dimensions	(WxHxD) 180x14x45 mm
Connections	NC, max. contact capacity 60 V DC/AC/1 A/10 W
Width	13 mm
Type of detection	Magnetic field measurement
Stray-field protection	No
Housing material	Aluminium
Height	230 mm
Cable type	4-core
Cable length	2 m

Length	45 mm
Max. operating temperature	50 °C
Installation location	Setup, optimal triggering clearance 20 mm
Tamper monitoring	Yes
IP protection class	65
Sensor type	Reed contact
Certifications	VdS B