



AMAZON SUBMERSIBLE & IN-LINE PUMP KIT

LVM-130

12 volt pump kit

LVM-131

24 volt pump kit



- ◆ Pumps fresh water, sea water and diesel
- ◆ Fast diesel refuelling and transfer with no spillage
- ◆ Bilge pump out in tight areas
- ◆ Water transfer; deck showers; and general wash-down
- ◆ Agricultural spraying, carboy and drum emptying and transfer
- ◆ Robust, slim line with clip-on easy clean filter


FLOW RATE:

Flow rate and current reduces as the height to be pumped increases


RECOMMENDED FUSE SIZE:

12 volt – 5 amp
24 volt – 3 amp

WEIGHT: 0.85kg



CONNECTIONS: for 12.7mm (1/2") bore hose



- ◆ Up to 18 litres (4.4 gallons) per minute
- ◆ Suitable for diesel fuel, water, seawater
- ◆ Temperatures up to 80°C
- ◆ Includes 4m lay-flat hose, adjustable spray nozzle, 4m electrical cable with crocodile clips
- ◆ Intermittent duty



Not suitable for pumping petrol, light hydrocarbons, non-aqueous solvents

Doc 664/13