

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: JENOLITE RED OXIDE PRIMER

Product code: 312758

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: PC9a: Coatings and paints, thinners, paint removers.

1.3. Details of the supplier of the safety data sheet

Company name: Jenolite UK Ltd
Chater Lea Buildings
Letchworth
Hertfordshire
SG6 1WT

Tel: 01462 480764

Email: Sales@Jenolite.net

1.4. Emergency telephone number

Emergency tel: 01462 480764
(office hours only)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Flam. Liq. 3: H226; Skin Irrit. 2: H315; Aquatic Chronic 3: H412; -: EUH208

Most important adverse effects: Contains 2-butanone oxime. May produce an allergic reaction. Flammable liquid and vapour. Causes skin irritation. Harmful to aquatic life with long lasting effects.

2.2. Label elements

Label elements:

Hazard statements: EUH208: Contains 2-butanone oxime. May produce an allergic reaction.

H226: Flammable liquid and vapour.

H315: Causes skin irritation.

H412: Harmful to aquatic life with long lasting effects.

Hazard pictograms: GHS02: Flame

GHS07: Exclamation mark



Signal words: Warning

SAFETY DATA SHEET

JENOLITE RED OXIDE PRIMER

Page: 2

Precautionary statements: P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P241: Use explosion-proof electrical/ventilating/lighting/... equipment.
P243: Take action to prevent static discharges.
P264: Wash contaminated skin thoroughly after handling.
P280: Wear protective gloves/protective clothing/eye protection/face protection.
P302+P352: IF ON SKIN: Wash with plenty of water.
P303+P361+P353: IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water .
P321: Specific treatment (see instructions on this label)
P332+P313: If skin irritation occurs: Get medical advice/attention.
P370+P378: In case of fire: Use media other than water to extinguish.
P501: Dispose of contents/container to comply with Local, National and International regulations.

Haz. ingredients (label): XYLENE; TOLUENE

2.3. Other hazards

Other hazards: In use, may form flammable / explosive vapour-air mixture.

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

XYLENE

EINECS	CAS	PBT / WEL	CLP Classification	Percent
215-535-7	1330-20-7	-	Flam. Liq. 3: H226; Acute Tox. 4: H332; Acute Tox. 4: H312; Skin Irrit. 2: H315	10-30%

TRIZINC BIS(ORTHOPHOSPHATE)

231-944-3	7779-90-0	-	Aquatic Chronic 1: H410; Aquatic Acute 1: H400	1-2.9%
-----------	-----------	---	--	--------

ETHYLBENZENE

202-849-4	100-41-4	-	Flam. Liq. 2: H225; Acute Tox. 4: H332; STOT RE 2: H373; Asp. Tox. 1: H304	1-2.9%
-----------	----------	---	--	--------

2-BUTANONE OXIME

202-496-6	96-29-7	-	Carc. 2: H351; Acute Tox. 4: H312; Eye Dam. 1: H318; Skin Sens. 1: H317	<1%
-----------	---------	---	---	-----

[cont...]

SAFETY DATA SHEET
JENOLITE RED OXIDE PRIMER

Page: 3

TOLUENE

203-625-9	108-88-3	-	Flam. Liq. 2: H225; Repr. 2: H361d; Asp. Tox. 1: H304; STOT RE 2: H373; Skin Irrit. 2: H315; STOT SE 3: H336	<1%
-----------	----------	---	--	-----

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Eye bathing equipment should be available on the premises.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Alcohol resistant foam. Water spray. Carbon dioxide. Dry chemical powder. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: Flammable. In combustion emits toxic fumes. Forms explosive air-vapour mixture.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn

[cont...]

SAFETY DATA SHEET

JENOLITE RED OXIDE PRIMER

Page: 4

leaking containers leak-side up to prevent the escape of liquid. Eliminate all sources of ignition.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method. Do not use equipment in clean-up procedure which may produce sparks.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Avoid the formation or spread of mists in the air. Smoking is forbidden. Use non-sparking tools.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed. Keep away from sources of ignition. Prevent the build up of electrostatic charge in the immediate area. Ensure lighting and electrical equipment are not a source of ignition.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

XYLENE

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	220 mg/m3	441 mg/m3	-	-

ETHYLBENZENE

UK	441 mg/m3	552 mg/m3	-	-
----	-----------	-----------	---	---

TOLUENE

UK	191 mg/m3	384 mg/m3	-	-
----	-----------	-----------	---	---

[cont...]

SAFETY DATA SHEET
JENOLITE RED OXIDE PRIMER

Page: 5

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. Ensure lighting and electrical equipment are not a source of ignition.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Red

Odour: Characteristic odour

Evaporation rate: No data available.

Oxidising: No data available.

Solubility in water: Not miscible

Boiling point/range°C: >35

Melting point/range°C: No data available.

Flammability limits %: lower: No data available.

upper: No data available.

Flash point°C: 23 - 60

Part.coeff. n-octanol/water: No data available.

Autoflammability°C: 500

Vapour pressure: 6.7 hPa @ 20degC

Relative density: 1.49

pH: No data available.

VOC g/l: No data available.

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions. Stable at room temperature.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.
Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat. Hot surfaces. Sources of ignition. Flames.

[cont...]

SAFETY DATA SHEET
JENOLITE RED OXIDE PRIMER

Page: 6

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

XYLENE

ORL	MUS	LD50	2119	mg/kg
ORL	RAT	LD50	4300	mg/kg
SCU	RAT	LD50	1700	mg/kg

ETHYLBENZENE

IPR	MUS	LD50	2624	µl/kg
ORL	RAT	LD50	3500	mg/kg

2-BUTANONE OXIME

ORL	MUS	LD50	1	gm/kg
ORL	RAT	LD50	930	mg/kg
SCU	RAT	LD50	2702	mg/kg

TOLUENE

IVN	RAT	LD50	1960	mg/kg
ORL	MUS	LD50	2	gm/kg
ORL	RAT	LD50	6900	mg/kg

Relevant hazards for product:

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

[cont...]

SAFETY DATA SHEET
JENOLITE RED OXIDE PRIMER

Page: 7

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN1263

14.2. UN proper shipping name

Shipping name: PAINT

14.3. Transport hazard class(es)

Transport class: 3

14.4. Packing group

Packing group: III

14.5. Environmental hazards

Environmentally hazardous: No

Marine pollutant: No

14.6. Special precautions for user

Special precautions: No special precautions.

[cont...]

SAFETY DATA SHEET
JENOLITE RED OXIDE PRIMER

Page: 8

Tunnel code: D/E

Transport category: 3

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: EUH208: Contains 2-butanone oxime. May produce an allergic reaction.

H225: Highly flammable liquid and vapour.

H226: Flammable liquid and vapour.

H304: May be fatal if swallowed and enters airways.

H312: Harmful in contact with skin.

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H318: Causes serious eye damage.

H332: Harmful if inhaled.

H336: May cause drowsiness or dizziness.

H351: Suspected of causing cancer.

H361d: Suspected of damaging the unborn child.

H373: May cause damage to organs through prolonged or repeated exposure.

H410: Very toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.