



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (40% in Component Part) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 103958-1  
[10X2 MTE RPT SR LATCH .100CL](#)




TE Part # 103970-1  
[10X2 MTE RCPT SR RIBBED .100CL](#)




TE Part # 103648-1  
[02 MTE RCPT HSG SR RIB .100CL](#)

Customers Also Bought



TE Part #6-240655-1  
[ANVIL](#)



TE Part #CG3226-000  
[CI-FH10050](#)



TE Part #3-1617119-1  
[J1MSCD-12XP = M39016/25-035P](#)



TE Part #2-1423678-1  
[W23-X1A1A-25=CKTBKR,THERM,PB,SCW,BUSH](#)



TE Part #T4161220004-003  
[RPC-M12-MR-4CON-PUR-1.5SH](#)



TE Part #456428-4  
[CRIMPER WIRE .180 F](#)



TE Part #YDTS20F11-05PDV001  
[RECP ASSY](#)



TE Part #6609000-6  
[3EEAP=F7650 S0](#)



TE Part #YDTS24W15-97SCV001  
[RECP ASSY](#)



TE Part #2-1423678-0  
[W23-X1A1A-20=CKTBKR,THERM,PB,SCW,BUSH](#)

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1375583-1\\_F.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1375583-1\\_F.3d\\_igs.zip](#)

English



Customer View Model

[ENG\\_CVM\\_CVM\\_1375583-1\\_F.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPMODU MTE INTERCONNECT SYSTEM](#)

English

Product Specifications

[Application Specification](#)

English