

CP1935 v1.5 RS 251-3772**SAFETY DATA SHEET****RS Pro Telephone Cleaning Wipes**

According to Regulation (EC) No 1907/2006, Annex II, as amended. Commission Regulation (EU) No 2015/830 of 28 May 2015.

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

Product name RS Pro Telephone Cleaning Wipes
Product number 251-3772, ZP
UFI UFI: 1YRA-R0MK-M001-KR35

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Cleaning agent.
Uses advised against No specific uses advised against are identified.

1.3. Details of the supplier of the safety data sheet

Supplier RS Components Ltd
 Birchington Road,
 Corby,
 Northants
 NN17 9RS
 +44 (0) 845 850 9900
 RCustomerServicesUK@rs-components.com

RS Components Ltd
 Glenview Industrial Estate
 Herberton Road
 Rialto
 Dublin 12
 +353 (0) 1 415 3100
 enquiries.ie@rs-components.com

1.4. Emergency telephone number

Emergency telephone IN CASE OF EMERGENCY CALL:
 +44 1865 407333
 +44 1235 239670

SECTION 2: Hazards identification**2.1. Classification of the substance or mixture****Classification (EC 1272/2008)**

Physical hazards Not Classified
Health hazards Eye Irrit. 2 - H319
Environmental hazards Not Classified

2.2. Label elements**Hazard pictograms**

Signal word Warning

RS Pro Telephone Cleaning Wipes

Hazard statements	EUH208 Contains 1,2-Benzisothiazol-3(2H)-one, Reaction mass of: 5-chloro-2-methyl-4-isothiazolin-3-one [EC no. 247-500-7] and 2-methyl-2H -isothiazol-3-one [EC no. 220-239-6] (3:1). May produce an allergic reaction. H319 Causes serious eye irritation.
Precautionary statements	P102 Keep out of reach of children. P264 Wash contaminated skin thoroughly after handling. P280 Wear protective gloves/ protective clothing/ eye protection/ face protection. P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P337+P313 If eye irritation persists: Get medical advice/ attention.
Detergent labelling	< 5% perfumes, Contains D-LIMONENE, BENZISOTHIAZOLINONE, METHYLISOTHIAZOLINONE, METHYLCHLOROISOTHIAZOLINONE AND METHYLISOTHIAZOLINONE

2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Propan-2-ol	10-30%
CAS number: 67-63-0	EC number: 200-661-7
	REACH registration number: 01-2119457558-25-XXXX
Classification	
Flam. Liq. 2 - H225	
Eye Irrit. 2 - H319	
STOT SE 3 - H336	
Benzyl-C12-14-alkyldimethylammonium chlorides	<1%
CAS number: 68424-85-1	EC number: 939-350-2
	REACH registration number: 01-2119970550-39-0000
M factor (Acute) = 10	M factor (Chronic) = 1
Classification	
Acute Tox. 4 - H302	
Skin Corr. 1B - H314	
Eye Dam. 1 - H318	
Aquatic Acute 1 - H400	
Aquatic Chronic 1 - H410	

RS Pro Telephone Cleaning Wipes

1,2-Benzisothiazol-3(2H)-one	<1%
CAS number: 2634-33-5	EC number: 220-120-9
M factor (Acute) = 1	
Classification	
Acute Tox. 4 - H302	
Skin Irrit. 2 - H315	
Eye Dam. 1 - H318	
Skin Sens. 1 - H317	
Aquatic Acute 1 - H400	
Ethanol	<1%
CAS number: 64-17-5	EC number: 200-578-6
	REACH registration number: 01-2119457610-43-XXXX
Classification	
Flam. Liq. 2 - H225	
Reaction mass of: 5-chloro-2-methyl-4-isothiazolin-3-one [EC no. 247-500-7] and 2-methyl-2H -isothiazol-3-one [EC no. 220-239-6] (3:1)	<1%
CAS number: 55965-84-9	
M factor (Acute) = 1	M factor (Chronic) = 1
Classification	
Acute Tox. 3 - H301	
Acute Tox. 3 - H311	
Acute Tox. 3 - H331	
Skin Corr. 1B - H314	
Eye Dam. 1 - H318	
Skin Sens. 1 - H317	
Aquatic Acute 1 - H400	
Aquatic Chronic 1 - H410	
2,6-Di-tert-butyl-p-cresol	<1%
CAS number: 128-37-0	EC number: 204-881-4
M factor (Acute) = 1	M factor (Chronic) = 1
Classification	
Aquatic Acute 1 - H400	
Aquatic Chronic 1 - H410	

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information

Get medical attention if any discomfort continues. Show this Safety Data Sheet to the medical personnel.

RS Pro Telephone Cleaning Wipes

Inhalation	Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Loosen tight clothing such as collar, tie or belt. Get medical attention if symptoms are severe or persist.
Ingestion	Rinse mouth thoroughly with water. Get medical advice/attention if you feel unwell. Do not induce vomiting unless under the direction of medical personnel.
Skin contact	Rinse with water.
Eye contact	Rinse with water. Do not rub eye. Remove any contact lenses and open eyelids wide apart. Get medical attention if any discomfort continues.
Protection of first aiders	First aid personnel should wear appropriate protective equipment during any rescue.

4.2. Most important symptoms and effects, both acute and delayed

General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	No specific symptoms known.
Ingestion	No specific symptoms known.
Skin contact	No specific symptoms known.
Eye contact	Irritating to eyes.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor	Treat symptomatically.
-----------------------------	------------------------

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	The product is not flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture

Specific hazards	Containers can burst violently or explode when heated, due to excessive pressure build-up.
Hazardous combustion products	Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

5.3. Advice for firefighters

Protective actions during firefighting	Avoid breathing fire gases or vapours. Evacuate area. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. If a leak or spill has not ignited, use water spray to disperse vapours and protect men stopping the leak. Control run-off water by containing and keeping it out of sewers and watercourses. If risk of water pollution occurs, notify appropriate authorities.
Special protective equipment for firefighters	Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Firefighter's clothing conforming to European standard EN469 (including helmets, protective boots and gloves) will provide a basic level of protection for chemical incidents.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

RS Pro Telephone Cleaning Wipes

Personal precautions Wear protective clothing as described in Section 8 of this safety data sheet. No action shall be taken without appropriate training or involving any personal risk. Do not touch or walk into spilled material.

6.2. Environmental precautions

Environmental precautions Avoid discharge into drains or watercourses or onto the ground.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Wear protective clothing as described in Section 8 of this safety data sheet. Clear up spills immediately and dispose of waste safely. If the product is soluble in water, dilute the spillage with water and mop it up. Alternatively, or if it is not water-soluble, absorb the spillage with an inert, dry material and place it in a suitable waste disposal container. The contaminated absorbent may pose the same hazard as the spilled material. Label the containers containing waste and contaminated materials and remove from the area as soon as possible. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. For waste disposal, see Section 13.

6.4. Reference to other sections

Reference to other sections For personal protection, see Section 8. See Section 11 for additional information on health hazards. See Section 12 for additional information on ecological hazards. For waste disposal, see Section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Keep out of the reach of children. Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Handle all packages and containers carefully to minimise spills. Keep container tightly sealed when not in use. Avoid the formation of mists.

Advice on general occupational hygiene Wash promptly if skin becomes contaminated. Take off contaminated clothing. Wash contaminated clothing before reuse.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Store away from incompatible materials (see Section 10). Keep out of the reach of children. Keep away from food, drink and animal feeding stuffs. Keep only in the original container. Keep container tightly closed, in a cool, well ventilated place. Keep containers upright. Protect containers from damage.

Storage class Chemical storage.

7.3. Specific end use(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure controls/Personal protection

8.1. Control parameters

Occupational exposure limits

Propan-2-ol

Long-term exposure limit (8-hour TWA): WEL 400 ppm 999 mg/m³

Short-term exposure limit (15-minute): WEL 500 ppm 1250 mg/m³

Ethanol

Long-term exposure limit (8-hour TWA): WEL 1000 ppm 1920 mg/m³

2,6-Di-tert-butyl-p-cresol

Long-term exposure limit (8-hour TWA): WEL 10 mg/m³

RS Pro Telephone Cleaning Wipes

WEL = Workplace Exposure Limit

8.2. Exposure controls

Protective equipment



Appropriate engineering controls	Provide adequate ventilation.
Eye/face protection	Avoid contact with eyes. Large Spillages: Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible.
Hand protection	No specific hand protection recommended.
Other skin and body protection	Appropriate footwear and additional protective clothing complying with an approved standard should be worn if a risk assessment indicates skin contamination is possible.
Hygiene measures	Wash hands thoroughly after handling. Do not eat, drink or smoke when using this product. Wash contaminated clothing before reuse.
Respiratory protection	No specific recommendations. Provide adequate ventilation. Large Spillages: If ventilation is inadequate, suitable respiratory protection must be worn.
Environmental exposure controls	Keep container tightly sealed when not in use. Avoid release to the environment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	Liquid-impregnated wipe.
Colour	Colourless.
Odour	Characteristic.
Odour threshold	Not available.
pH	pH (concentrated solution): 5-6
Melting point	Not available.
Initial boiling point and range	Not available.
Flash point	Not available.
Evaporation rate	Not available.
Evaporation factor	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	Not available.
Other flammability	Not available.
Vapour pressure	Not available.
Vapour density	Not available.
Relative density	Not available.
Bulk density	Not available.

RS Pro Telephone Cleaning Wipes

Solubility(ies)	Not available.
Partition coefficient	Not available.
Auto-ignition temperature	Not available.
Decomposition Temperature	Not available.
Viscosity	Not available.
Explosive properties	Not considered to be explosive.
Oxidising properties	Does not meet the criteria for classification as oxidising.

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity See the other subsections of this section for further details.

10.2. Chemical stability

Stability Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions No potentially hazardous reactions known.

10.4. Conditions to avoid

Conditions to avoid There are no known conditions that are likely to result in a hazardous situation.

10.5. Incompatible materials

Materials to avoid No specific material or group of materials is likely to react with the product to produce a hazardous situation.

10.6. Hazardous decomposition products

Hazardous decomposition products Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity - oral

Notes (oral LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - dermal

Notes (dermal LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - inhalation

Notes (inhalation LC₅₀) Based on available data the classification criteria are not met.

Skin corrosion/irritation

Animal data Based on available data the classification criteria are not met.

Serious eye damage/irritation

Serious eye damage/irritation Causes serious eye irritation.

Respiratory sensitisation

Respiratory sensitisation Based on available data the classification criteria are not met.

RS Pro Telephone Cleaning Wipes

Skin sensitisation

Skin sensitisation Based on available data the classification criteria are not met.

Germ cell mutagenicity

Genotoxicity - in vitro Based on available data the classification criteria are not met.

Carcinogenicity

Carcinogenicity Based on available data the classification criteria are not met.

IARC carcinogenicity

None of the ingredients are listed or exempt.

Reproductive toxicity

Reproductive toxicity - fertility Based on available data the classification criteria are not met.

Reproductive toxicity - development

Based on available data the classification criteria are not met.

Specific target organ toxicity - single exposure

STOT - single exposure Not classified as a specific target organ toxicant after a single exposure.

Target organs

Central nervous system

Specific target organ toxicity - repeated exposure

STOT - repeated exposure Not classified as a specific target organ toxicant after repeated exposure.

Aspiration hazard

Aspiration hazard Based on available data the classification criteria are not met.

General information

The severity of the symptoms described will vary dependent on the concentration and the length of exposure.

Inhalation

No specific symptoms known.

Ingestion

No specific symptoms known.

Skin contact

No specific symptoms known.

Eye contact

Irritating to eyes.

Route of exposure

Ingestion Inhalation Skin and/or eye contact

Target organs

No specific target organs known.

SECTION 12: Ecological information

Ecotoxicity

Not regarded as dangerous for the environment. However, large or frequent spills may have hazardous effects on the environment.

12.1. Toxicity

Toxicity

Based on available data the classification criteria are not met.

12.2. Persistence and degradability

Persistence and degradability

The degradability of the product is not known.

12.3. Bioaccumulative potential

Bioaccumulative potential

No data available on bioaccumulation.

Partition coefficient

Not available.

12.4. Mobility in soil

RS Pro Telephone Cleaning Wipes

Mobility No data available.

12.5. Results of PBT and vPvB assessment

12.6. Other adverse effects

Other adverse effects None known.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information The generation of waste should be minimised or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way. When handling waste, the safety precautions applying to handling of the product should be considered. Care should be taken when handling emptied containers that have not been thoroughly cleaned or rinsed out. Empty containers or liners may retain some product residues and hence be potentially hazardous.

Disposal methods Do not empty into drains. Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

SECTION 14: Transport information

General The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).

14.1. UN number

Not applicable.

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

No transport warning sign required.

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Not applicable.

**Annex II of MARPOL 73/78
and the IBC Code**

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations Health and Safety at Work etc. Act 1974 (as amended).
The Carriage of Dangerous Goods and Use of Transportable Pressure Equipment Regulations 2009 (SI 2009 No. 1348) (as amended) ["CDG 2009"].
EH40/2005 Workplace exposure limits.

RS Pro Telephone Cleaning Wipes

EU legislation

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended).
 Commission Regulation (EU) No 2015/830 of 28 May 2015.
 Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended).

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

Inventories

EU - EINECS/ELINCS

None of the ingredients are listed or exempt.

SECTION 16: Other information

Abbreviations and acronyms used in the safety data sheet

ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road.
 ADN: European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways.
 RID: European Agreement concerning the International Carriage of Dangerous Goods by Rail.
 IATA: International Air Transport Association.
 ICAO: Technical Instructions for the Safe Transport of Dangerous Goods by Air.
 IMDG: International Maritime Dangerous Goods.
 CAS: Chemical Abstracts Service.
 ATE: Acute Toxicity Estimate.
 LC₅₀: Lethal Concentration to 50 % of a test population.
 LD₅₀: Lethal Dose to 50% of a test population (Median Lethal Dose).
 EC₅₀: 50% of maximal Effective Concentration.
 PBT: Persistent, Bioaccumulative and Toxic substance.
 vPvB: Very Persistent and Very Bioaccumulative.

Classification abbreviations and acronyms

Eye Irrit. = Eye irritation

Classification procedures according to Regulation (EC) 1272/2008

Eye Irrit. 2 - H319: : Calculation method.

Training advice

Read and follow manufacturer's recommendations.

Issued by

Emily Kirk

Revision date

11/11/2019

Revision

2.2

SDS number

1095

RS Pro Telephone Cleaning Wipes

Hazard statements in full

H225 Highly flammable liquid and vapour.
H301 Toxic if swallowed.
H302 Harmful if swallowed.
H311 Toxic in contact with skin.
H314 Causes severe skin burns and eye damage.
H315 Causes skin irritation.
H317 May cause an allergic skin reaction.
H318 Causes serious eye damage.
H319 Causes serious eye irritation.
H331 Toxic if inhaled.
H336 May cause drowsiness or dizziness.
H400 Very toxic to aquatic life.
H410 Very toxic to aquatic life with long lasting effects.
EUH208 Contains 1,2-Benzisothiazol-3(2H)-one, Reaction mass of: 5-chloro-2-methyl-4-isothiazolin-3-one [EC no. 247-500-7] and 2-methyl-2H -isothiazol-3-one [EC no. 220-239-6] (3:1). May produce an allergic reaction.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.