


Approvals:  



Rewirable Inlets

Specifications

Contact Resistance (Initial):	10 mohms max.
Reference Standard:	IEC 60320-1
Mounting:	Rewirable
Terminals:	Screw-type
Panel Thickness:	NA
Permissible temperature - For soldering:	270 deg. C for 5 sec. max.
Permissible temperature - With/without load:	0 to 70 deg C
Material - Terminals:	Copper Alloy, Tin plating
Material - Body:	Nylon-6 20% GF V2
HV Breakdown test for 1 Minute:	2 KV AC
Insulation Resistance at 500 VDC:	1000 M ohms Min.
Current & voltage rating:	16 Amp (VDE), 250 VAC
Approvals:	VDE, CE