




Connectors > PCB Connectors > Backplane Connectors > Backplane Connector Housings



Number of Positions: 60

Connector System: Board-to-Board

Row-to-Row Spacing: 2 mm

Number of Rows: 5

Number of Columns: 12

Features

Product Type Features

Connector System	Board-to-Board
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	60
Number of Rows	5
Number of Columns	12

Contact Features

Contact Current Rating (Max)	1 A
------------------------------	-----

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

--	--



Centerline (Pitch)	2 mm
--------------------	------

Dimensions

Row-to-Row Spacing	2 mm
--------------------	------

Usage Conditions

Operating Temperature Range	-67 – 257 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance


For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Pin-in-Paste capable to 260°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 5223002-2
FB-5R,ASY,060,SIG,HDR,EN,4.25




TE Part # 3-5223081-1
2MM FB ASY HDR SIG 5R 60 PSN 5




TE Part # 5223524-2
2MMFB,5R,ASY,060,SIG,HDR,EN




TE Part # 5223016-2
FB-5R,ASY,060,SIG,HDR,EN,4.25



TE Part # 5223011-2
FB-5R,ASY,060,SIG,HDR,SL,4.25




TE Part # 5223010-2
FB-FR,ASY,060,SIG,HDR,SL,4.25




TE Part # 5223000-2
FB-5R,ASY,060,SIG,HDR,SL,4.25


Also in the Series | Z-PACK Future Bus+




Backplane Connector Housings(19)



Board-to-Board Headers & Receptacles(14)



Hard Metric Backplane Connectors(1)



PCB Headers & Receptacles(14)




Rectangular Power Connectors(14)

Customers Also Bought



TE Part #1-179228-0
CT CRIMP-2 REC HSG 10P NATURAL



TE Part #104130-2
014 LOPRO HDR RA 30DP LATCH



TE Part #2007394-5
SFP+assy 2x4 Spring Fingers 4



TE Part #1934222-1
Tin Man Recpt Assy 4Pair8Column




TE Part #1981584-1
MICRO USB, TYPE A/B, GRAY



TE Part #1410187-3
MULTIGIG RT T2 7RW DC DF CT



TE Part #1410189-3
MULTIGIG RT T2 7RW H-LFT,ET2



TE Part #5111448-1
010 UNIV I/O 30DP SLOT



TE Part #5228979-7
JACK,COML,SERIES BNC,GOLD PL



TE Part #2157553-1
RF BACKPLANE MODULE 8 POS

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5223004-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5223004-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5223004-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English