

FEATURES

- **2.5 m cable length:** Provides ample reach for connecting devices at a distance.
- **IEC C13 to CEE 7 connectors:** Ensures compatibility with a wide range of equipment.
- **16 A current rating:** Supports high-power devices safely.
- **Polyvinyl Chloride jacket:** Offers durability and resistance to wear and tear.
- **Right angle plug:** Facilitates connections in tight spaces.
- **250 V voltage rating:** Suitable for standard voltage applications.

RS PRO 2.5 m Power Cable, IEC C13 to CEE 7

RS Stock No: 558-957



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO power cable is designed for reliable electrical connections in various industrial and commercial settings. With a length of 2.5 metres, it offers flexibility and ease of use in connecting devices to power sources. The cable is ideal for applications requiring a robust and durable connection, ensuring efficient power delivery.

General Specifications

Connector Type A	IEC C13
Connector Type B	CEE 7
Jacket Colour	Grey
Mains Socket Type	Straight
Product Type	Power Cable

Mechanical Specifications

Cable Length	2.5 m
Jacket Material	Polyvinyl Chloride

Electrical Specifications

Current Rating	16 A
Mains Plug Type	Right Angle Plug
Voltage	250 V

Approvals

Standards/Approvals	CCCs, CEBEC, CSA, D, EAC, ENEC 11, FI, ICC, IMQ, JET, KEMA, KEUR, N, NF, OVE, PSE, RCM N10544, S, SII, UL, VDA
---------------------	----------------------------------------------------------------------------------------------------------------