


IO-Link CompactLine module

IO-Link Module 10x2 DO M12 IP67



Application

Application

I/O modules for field applications

Electrical data

Operating voltage	[V]	18...30 DC; (US)
Current consumption	[mA]	50; (US)
Protection class		III
Additional voltage supply	[V]	18...30 DC; (UA)
Max. current consumption from additional supply	[mA]	3600; (UA)



IO-Link CompactLine module

IO-Link Module 10x2 DO M12 IP67

Inputs / outputs			
Number of inputs and outputs		Number of digital outputs: 20	
Outputs			
Number of digital outputs		20; (10 x 2)	
Circuit		PNP	
Output function		transistor	
Max. current load per output [mA]		1800	
Max. current load outputs total [A]		3.6; (Max. current load per output side: 1800 mA)	
Electrically separated		yes	
Interfaces			
Communication interface		IO-Link	
Supported DeviceIDs		Type of operation	DeviceID
		default	893
IO-Link Device			
Transmission type		COM2 (38,4 kBaud)	
IO-Link revision		1.1	
SDCI standard		IEC 61131-9	
SIO mode		no	
Min. process cycle time [ms]		5.6	
Operating conditions			
Ambient temperature [°C]		-25...60	
Storage temperature [°C]		-25...70	
Max. relative air humidity [%]		90	
Max. height above sea level [m]		2000	
Protection		IP 65; IP 67	
Protection rating (NEMA 250)		6P	
Pollution degree		2	
Chemical media		ISO 16750-5	AA, BA, BD, HLP, CC, DB, DC, DD, CA
		NEMA 250 5.13.1	AA
Tests / approvals			
EMC		EN 61000-6-2	
		EN 61000-6-3	
		IEC 61131-9	
Shock resistance		DIN EN 60068-2-27	
Vibration resistance		DIN EN 60068-2-64	
		DIN EN 60068-2-6	
MTTF [years]		41	
Mechanical data			
Weight [g]		408	
Housing		rectangular	
Type of mounting		backplane mounting	
Dimensions [mm]		208 x 59.3 x 38.4	
Materials		housing: PA; socket: brass nickel-plated	



IO-Link CompactLine module

IO-Link Module 10x2 DO M12 IP67

Sealing material	FKM
------------------	-----

Displays / operating elements

Display	operation	LED, green
	errors	LED, red
	function	LED, yellow

Accessories

Accessories (optional)	Protective caps M12
------------------------	---------------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - IO-Link

Connector: M12; coding: A




X1

1	+ 24 V DC (US)
2	not used
3	GND (US)
4	IO-Link

Electrical connection - Outputs

Connector: M12; coding: A; Sealing: FKM



X1.0...X1.9

1	not used
2	DO2
3	GND (UA)
4	DO1
5	not used



IO-Link CompactLine module

IO-Link Module 10x2 DO M12 IP67

Electrical connection - power supply

Connector: M12; coding: A



X31

1	+ 24 V DC (UAL)
2	GND (UAR)
3	GND (UAL)
4	+ 24 V DC (UAR)