

TF-K5

Torque wrench TORCOFIX TF-K

20-850 Nm / 15-630 lbf·ft

Code ETIM
3288226 EC002132

EAN UNSPSC
4010886965559 27-11-17-15

Country of origin eCI@ss
Germany 21-04-02-22

Customs tariff number
82041100



Article description

- Use:
- Controlled screw tightening in the range of 1 - 5 Nm / 0,75 - 3,7 lbf·ft
- Adjustable, releasing and sturdy tubular torque wrench with integrated ratchet and with square drive for industry and the trades
- Features:
- Classified as per DIN EN ISO 6789-2:2017 Type II Class A; adjusted to a maximum permissible +/- 3 % deviation and thus with a greater precision than the standard-stipulated +/- 6 %
- Incl. traceable test certificate (DIN EN ISO 6789-2:2017)
- For controlled right- and left-hand tightening (square socket for direction change)
- 1/4" mushroom head socket square with ball lock
- Robust, matt powder-coated tubular steel construction, with galvanized ratchet and high-quality plastic parts
- New ergonomic handle, shaped according to the natural grip position of the hand
- clearly recognisable and tactile hand centring aid and calibration aid in the middle of the handle
- Double scale Nm / lbf·ft and vernier are protected from abrasion and contamination by an enlarged viewing window
- With vernier scale for Nm main scale for setting intermediate scale values; lbf·ft setting only via main scale
- Vertical alignment of the scale, torque adjustment therefore suitable for left and right handers
- Scale line positioned directly above the scale prevents reading errors (parallax errors)
- Unit labeling integrated in the scale frame and also protected by viewing windows
- The precise release mechanism generates a distinct tactile and audible release signal when the set torque value is reached
- incl. roll away protection, prevents rolling away when the tool is put down

Article information

Contents (Qty of pieces)	1	Torque range (min./max.) [N·m]	1 Nm - 5 Nm
Net weight [kg]	0,33 kg	Torque range (min./max.) [lbf·ft]	0,75 lbf·ft - 3,7 lbf·ft
Total length [mm]	223 mm	Trigger mechanism	Short path triggering
Total width [mm]	39 mm	Precision +/-	+/- 3 %
Total height [mm]	39,8 mm	Direction of tightening	Left and right
Material	Tubular steel construction, top-grade plastic parts	Fixed setting	no
Standard	DIN 3120 - A 6,3 ISO 1174	Test certificate	DIN EN ISO 6789-2:2017
Drive connector square (male)	1/4"	Graduation	0,25
Drive connector square (male)	6,3 mm	Head height l [mm]	25,3 mm
Return angle	10 °	Width of head l [mm]	35,0 mm
Number of teeth	36	Calibration length	150,5 mm
Drive type/drive	Mushroom head	Graduation [lbf·ft]	25 lbf·ft
Torque (min.) [N·m]	1 Nm	Graduation [n·m]	0,25 Nm
Torque (max.) [N·m]	5 Nm	vernier Nm	0,025 Nm
Torque (min.) [lbf·ft]	0,75 lbf·ft	Distance housing - square drive	17,5 mm
Torque (max.) [lbf·ft]	3,7 lbf·ft	Storage/Content	Plastic box