

CR1F400FZ7

bistable contactor CR1-F - 3 poles - AC-3 440V
400 A - coil 110 V



Main

Range	TeSys
Product name	TeSys F
Product or component type	Magnetic contactor
Device short name	CR1F
Utilisation category	AC-1 AC-4 AC-3
Poles description	3P
Power pole contact composition	3 NO
[Ue] rated operational voltage	Power circuit: 1000 V AC Power circuit: 1000 V DC
[Ie] rated operational current	370 A (at <40 °C) AC/DC AC-4 for power circuit 400 A (at <40 °C) AC/DC AC-3 for power circuit 500 A (at <40 °C) AC/DC AC-1 for power circuit
[Uc] control circuit voltage	110 V DC
[Ith] conventional free air thermal current	500 A (at 40 °C) for power circuit
Irms rated making capacity	4500 A for power circuit
Rated breaking capacity	1200 A at 1000 V for power circuit 3000 A at 600...690 V for power circuit 3500 A at 500 V for power circuit 4000 A at 220...440 V for power circuit
Associated fuse rating	400 A aM for power circuit 500 A BS88 for power circuit 500 A gG for power circuit
Average impedance	0.28 Ohm - Ith 500 A 50 Hz for control circuit
[Ui] rated insulation voltage	Control circuit: 1000 V conforming to BS 775 Control circuit: 1000 V conforming to IEC 60158-1 Control circuit: 1000 V conforming to IEC 60947-4 Control circuit: 1500 V conforming to VDE 0110 group C
Power dissipation per pole	45 W AC-3 70 W AC-1 66 W AC-4
Standards	EN/IEC 60947-1 EN/IEC 60947-4-1 JIS C8201-4-1 UL 60947-4-1 CSA C22.2 No 60947-4-1
Product certifications	CB Scheme[RETURN]UL[RETURN]CSA[RETURN]EAC[RETURN]CE
Connections - terminals	Bolted connection
Operating time	40...75 ms latching 50...100 ms unlatching
Mechanical durability	1000000 cycles
Maximum operating rate	120 cyc/mn 40 °C
Coil type	Low consumption

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company mentioned herein. This information is not intended as a substitute for the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. It is the duty of any such user or integrator to perform these operations. The company mentioned herein and its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.






Complementary

Control circuit voltage limits	Latching: 0.85...1.1 Uc Unlatching: 0.85...1.1 Uc
Average consumption	500 W DC latching 70 W DC unlatching

Environment

Protective treatment	TH
Ambient air temperature for operation	-15...70 °C
Operating altitude	3000 m without derating
Operating position	+/- 5°
Height	375 mm
Width	261 mm
Depth	219 mm
Net weight	9.1 kg
Quantity per set	Set of 10

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins