


Titan anatomical tweezers 145 mm form 40 serrated

Art.-No.	5-036
Description	Titan anatomical tweezers 145 mm form 40 serrated
Application	Electronics, SMD/THT assembly, precision mechanics, watchmakers, jewelers, medical technology.
Specification	with serration
Material	Titan
Surface/Coating	matt finish
Features	antibacterial, antimagnetic, heat-resistant, solder-repellent:acid-resistant, non-reflecting, stainless, seawater resistant
Surface resistance	/
Shape	NG: Normal tips straight
Icon No.	NG5

Dimensions and weight

A = 18 mm
B = 2.5 mm
Ai = /



length 145 mm
weight 15 g

Application and technical data

Tweezers are made entirely of TITAN (light metal) and meet the highest technical requirements. Melting point 1941 K (1668°C), thermal conductivity 22W, electrical conductivity 2.5×10^6 .