

1544316-1 ✓ ACTIVE

## NG Power Terminals and Connectors, NG1

TE Internal #: 1544316-1

Single Wire Seal (SWS), 10.5 mm [.413 in] Cavity Diameter, -40 – 125 °C [-40 – 257 °F], Green, Silicone, NG Power Terminals and Connectors

[View on TE.com >](#)



[Connectors >](#) [Connector Accessories >](#) [Connector Seals & Cavity Plugs >](#) [Medium Power Terminals Single Wire Seals 4.8mm-12mm](#)



Connector Seal & Plug Type: **Single Wire Seal (SWS)**

Cavity Diameter: **10.5 mm [.413 in]**

Operating Temperature Range: **-40 – 125 °C [-40 – 257 °F]**

Primary Product Color: **Green**

Primary Product Material: **Silicone**

[All Medium Power Terminals Single Wire Seals 4.8mm-12mm \(9\)](#)

## Features

### Product Type Features

Connector Seal & Plug Type	Single Wire Seal (SWS)
----------------------------	------------------------

### Body Features

Primary Product Color	Green
Primary Product Material	Silicone

### Dimensions

Cavity Diameter	10.5 mm [.413 in]
Compatible Insulation Diameter Range	3.2 – 4.1 mm [.126 – .161 in]

### Usage Conditions

Operating Temperature Range	-40 – 125 °C [-40 – 257 °F]
Operating Temperature (Max)	125 °C [257 °F]

### Other

Resistance to Hydrocarbons	Poor
Shore A Hardness	50
Contains Lubricant	Yes

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 1544601-3  
RECEPTACLE HOUSING, 8MM NG1, 1 WAY



TE Part # 1544606-1  
TAB HOUSING, 8MM NG1, 1 WAY



TE Part # 1544334-3  
PL 2V 8MM NG1 MONT



TE Part # 1544965-2  
8MM NG1+ TERMINAL



TE Part # 1544964-2  
8MM NG1+ TERMINAL



TE Part # 1544603-2  
1W 8MM NG1 SEALED CLIP ASSY BLUE








TE Part # 1544434-1  
BOITIER PC 2 VOIES



TE Part # 1544969-1  
TAB, 8MM NG1 PLUS




Also in the Series | **NG1**



Also in the Series | **NG Power Terminals and Connectors**



Automotive Connector Caps & Covers (1)



Automotive Housings(47)



Automotive Terminals(25)



Connector Seals & Cavity Plugs(9)




Insertion & Extraction Tools(13)



Other Automotive Connector Accessories(1)

## Customers Also Bought




TE Part #1544606-1  
TAB HOUSING, 8MM NG1, 1 WAY



TE Part #4-1904124-4  
V23074H1005A502-EV-CBOX




TE Part #1544650-1  
PC 2V 8NG1 NOIR JT



TE Part #1544606-1  
TAB HOUSING, 8MM NG1, 1 WAY



TE Part #CAT-HST-ES1000  
ES1000 Heat Shrink Tubing




TE Part #1719105-2  
14POS,JPT,REC. HSG




TE Part #8-1625963-6  
HSA5 330R 5%



TE Part #2103943-2  
CU ALLOY, OUTER FERRULE, SIZE B



TE Part #2229097-1  
0.50 SERIES CONN 21POS PLUG ASSY



TE Part #1-2434680-1  
2POS, MQS, TAB HSG, COD A

## Documents



## Product Drawings

### JOINT VERT G2

English

---

## CAD Files

Customer View Model

[ENG\\_CVM\\_1544316-1\\_C.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_1544316-1\\_C.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_1544316-1\\_C.2d\\_dxf.zip](#)

English

[3D PDF](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

## Product Specifications

[Product Specification](#)

French