


Mikroborrar

Spårutförande	Höger, normalspiral
Skaftdiameter	1 mm
Spetsvinkel	118°
Ytbehandling	Blank
Användningsområde	För precisionsborring med små diametrar.


Mikroporat

Lastu-uran muoto	Oikeak. vakio kierukkakulma
Varren halkaisija	1.0mm
Kärkikulma	118°
Pintakäsittely	Kirkas
Käyttöalue	Pienten tarkkuusreikien poraukseen.


Micro Drills

Flute Geometry	Standard Helix, Right Hand Spiral.
Shank Diameter	1.0mm
Point Angle	118°
Surface Treatment	Bright
Application	For fine precision drilling

Entry Code	d ₁ Ø mm	d ₂ Ø _{h8} mm	l ₂ mm	l ₁ mm
A720.15	0,15	1	1,0	25
A720.18	0,18	1	1,4	25
A720.2	0,20	1	1,8	25
A720.22	0,22	1	1,8	25
A720.25	0,25	1	2,2	25
A720.28	0,28	1	2,2	25

Entry Code	d ₁ Ø mm	d ₂ Ø _{h8} mm	l ₂ mm	l ₁ mm
A720.3	0,30	1	2,2	25
A720.35	0,35	1	2,8	25
A720.38	0,38	1	2,8	25
A720.4	0,40	1	3,6	25
A720.45	0,45	1	3,6	25
A720.5	0,50	1	4,0	25
A720.6	0,60	1	4,5	25