



- NOTE
- LEAD CO-PLANARITY IS 0.1mm MAX.
 - THIS IS PACKAGED IN TRAY. (50pcs/TRAY)
 - FLOATING RANGE OF THIS CONNECTOR IS ± 0.8 mm MAX. IN THE X DIRECTION AND ± 0.6 mm MAX. IN THE Y DIRECTION.
 - BLEMISH AND HIT MARK CAN BE OCCURED THROUGH OUT THE MANUFACTURING PROCESS WHICH DOESN' T AFFECT QUALITY LEVEL.
 - PLEASE NOTE THAT EXCESSIVE WRENCHING FORCE COULD DAMAGE THIS CONNECTOR. PLEASE REFER TO THE GUIDELINE FOR DETAILED REGULATIONS OF THE MATING METHOD.
 - THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCES.

2	POLYAMIDE	BLACK	UL94V-0	4	BRASS	TIN-PLATING $1 \mu m$		
1	POLYAMIDE	BLACK	UL94V-0	3	COPPER ALLOY	CONTACT AREA: GOLD $0.1 \mu m$		
						LEAD AREA: GOLD $0.03 \mu m$		
						UNDER PLATING: NICKEL $1 \mu m$		
NO.	MATERIAL	FINISH	REMARKS	NO.	MATERIAL	FINISH	REMARKS	
UNITS		SCALE	COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE
mm		2 : 1						
APPROVED : HS. OKAWA				13.05.07		DRAWING NO.		EDC3-336330-00
CHECKED : KI. HIROKAWA				13.05.07		PART NO.		FX20-140P-0.5SV20
DESIGNED : TS. OONO				13.05.07		CODE NO.		CL570-1012-7-00
DRAWN : TS. OONO				13.05.07				