



Description

A highly versatile, 5 figure stroke counter. Numbers are large and distinctive for easy viewing even when above or below eye level. Ruggedly built for years of trouble-free use. An excellent choice for counting parts produced.

Features

- Durable
- Large figures
- Reliable

Options

- Large reset knob

Specifications

Figures: 5 figures, white on black, 0.19" [5mm] high
Reset: Knob
Speed: 500 counts/minute
Rotation: Top-coming or top-going
Count Stroke: 49° Min. - 60° Max.

Shaft Extension: Right-hand
Shaft Diameter: 0.125" [3.2mm]
Operating Life: Beyond 10 million counts
Temp. Range: -15°F to +140°F [-26°C to +60°C]
Weight: 1.5 oz. [43g]

Models Description


1-2035 Right-hand, top-coming, standard reset knob

Models Description

* Items in bold are normally in factory stock.

Dimensions


Right-Hand Shaft




Mounting holes: 0.13" x 0.38" [3.3 x 9.7mm] slots

Applications

Punch press



Machine cycles



Secondary machines

