


C4AT, Film, Metallized Polypropylene, Power, 5 uF, 5%, 350 VAC, 600 VDC, 70°C, Lead Spacing = 37.5mm



Dimensions

L	41.5mm NOM
H	40mm NOM
T	20mm NOM
S	37.5mm +/-0.4mm
S1	10.2mm +/-0.4mm
LL	6mm -2mm
F	1.2mm NOM

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	58

General Information

Supplier:	KEMET
Series:	C4AT
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	Switching
RoHS:	Yes
Lead:	4 Wire Leads

Specifications

Capacitance:	5 uF
Capacitance Tolerance:	5%
Voltage AC:	350 VAC
Voltage DC:	600 VDC
Temperature Range:	-40/+85C
Rated Temperature:	70°C
Dissipation Factor:	0.05%
Max dV/dt:	70 V/us
Resistance:	3.1 mOhms (100kHz)
Ripple Current:	22 Amps (100kHz 70C), 351 Amps (Peak)