



Main

Range of product	EZD
Product or component type	Circuit breaker
Device short name	Vigi EZD250M
Circuit breaker application	Distribution
Poles description	4P
Protected poles description	3d

Complementary

Earth-leakage protection	With
[In] rated current	250 A 40 °C
Breaking capacity code	M
Network type	AC
Network frequency	50/60 Hz
Control type	Toggle
Mounting mode	Fixed
Mounting support	Backplate
Upside connection	Front
Downside connection	Front
[Ui] rated insulation voltage	440 V EN/IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kV EN/IEC 60947-2
[Ue] rated operational voltage	440 V EN/IEC 60947-2 AC 50/60 Hz
Breaking capacity	36 kA Icu EN/IEC 60947-2 380/415 V AC 50/60 Hz 85 kA Icu EN/IEC 60947-2 220/230 V AC 50/60 Hz 25 kA Icu EN/IEC 60947-2 440 V AC 50/60 Hz
[Ics] rated service breaking capacity	43 kA EN/IEC 60947-2 220/230 V AC 50/60 Hz 13 kA EN/IEC 60947-2 440 V AC 50/60 Hz 18 kA EN/IEC 60947-2 380/415 V AC 50/60 Hz
Mechanical durability	10000 cycles
Electrical durability	5000 cycles EN/IEC 60947-2 440 V In
Connection pitch	35 mm
Trip unit name	TM-D
Trip unit technology	Thermal-magnetic
Trip unit rating	250 A 40 °C
Protection type	Earth-leakage protection Overload protection (thermal) Short-circuit protection (magnetic)
Long time pick-up adjustment type Ir	Fixed
Long time pick-up adjustment range	1 In
Instantaneous pick-up adjustment type Ii	Fixed
Integral instant protection	2500 kA
Residual earth-leakage sensitivity adjustment type	Adjustable 4 settings

[Δn] residual earth-leakage sensitive adjustment	0.5 A 0.1 A 1 A 0.3 A
Residual earth-leakage time delay adjustment type	Adjustable 4 settings
[Δt] residual earth-leakage time delay adjustment	200 ms 0 ms 1000 ms 500 ms
Height	165 mm
Width	140 mm
Depth	68 mm
Product weight	2.1 kg
Compatibility code	EZD250

Environment

Standards	IEC 60947-2 EN 60947-2
Pollution degree	3 IEC 60947-1
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0726 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available