

Signal lamp with integrated filament lamp, 5 mm, round bezel, 24 Volt, bezel slate gray, Solder terminal

DISCONTINUED**fields of application**

- Measurement-control-regulation
- Electrical engineering
- Mechanical and system engineering
- Signalling systems
- Model construction

**description**

Signal lamps with integrated filament lamp, mounting hole diameter 5 mm

technical data**➤ general**

Bezel color	slate gray
Property of bezel / mushroom	transparent
Bezel shape	round
illuminated	Yes
Packaging unit	10 pcs.
net weight	0.4 g
Degree of protection, front side, according to DIN EN 60529	IP40
MOQ order	50 pcs.
RoHS compliant	Yes
REACH compliant	Yes

➤ mounting diameters

Outside dimension, length	5.8 mm
Outside dimension, width	5.8 mm
Outside dimension, height	19 mm
Mounting hole	5 mm
Mounting depth	18 mm
Installation height	1 mm
Collar dimension	5.8 mm

direct links

- [RAFI eCatalog](#)

> mechanical data

Fixing	Pushing into mounting hole
Solderability	Yes
Terminal on the rear	Solder terminal

> electrical data

Operating voltage of the luminous element, max.	24 V
---	------

drawings

Mounting hole drawing

