

General Information

Extended Product Type:	S800-RHE-S
Product ID:	1SDA060179R0001
EAN:	8015644626242
Catalog Description:	S800-RHE-S Axial extension with a length of 500mm and a diameter of 6 x 6 mm
Long Description:	The S800-RHE-S is an axial extension for door assembly. It has to be used together with S800-RD the rotary drive adapter for 2- to 4-pole S800 and with either the red rotary drive S800-RHE-EM or the black one S800-RHE-H. The axial extension has a length of 500mm and a diameter of 6 x 6mm.

Categories

Products » Low Voltage Products and Systems » Modular DIN Rail Products » High Performance Circuit Breakers HPCBs Accessories

Ordering

EAN:	8015644626242
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85389040

Dimensions

Product Net Width:	6 mm
Product Net Height:	6 mm
Product Net Depth:	500 mm
Product Net Weight:	0.2 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	49 mm
Package Level 1 Height:	33 mm
Package Level 1 Length:	33 mm
Package Level 1 Gross Weight:	0.23 kg
Package Level 1 EAN:	8015644626242

Environmental

Ambient Air Temperature:	Operation -25 ... +60 °C Storage -40 ... +70 °C
Resistance to Shock acc. to IEC 60068-2-27:	5 g 30 ms
Resistance to Vibrations acc. to IEC 60068-2-6:	2 - 13.2 Hz / 1mm 13.2 - 100Hz / 0.7g with load 100% x Ie
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Additional Information

Product Main Type:	Accessories for High Performance Circuit Breakers HPCBs
Product Name:	Accessories for High Performance Circuit Breakers HPCBs
Remarks:	Can be used together with S800-RHE-EM or S800-RHE-H (rotary handle) and the S800-RD (rotary drive adapter for 2-4-pole S800)

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	2CCC413003C0203
Declaration of Conformity - CE:	N/A
RoHS Information:	2CCC413008D0204

Classifications

ETIM 4.0:	EC000230 - Door coupling handle for switchgear
ETIM 5.0:	EC000230 - Door coupling handle for switchgear
Object Classification Code:	F

