

Product datasheet

Specifications



gearbox straight teeth GBX - Ø 40 mm - reduction 5:1 < 15 arc.min - 14 N.m

GBX040005K

⚠ Discontinued on: 9 Feb 2023

⚠ Discontinued

EAN Code: 3606480388163

Main

Range compatibility	Lexium 28 Lexium SD3 Lexium ILE
Gear box type	Straight teeth
Product or component type	Planetary gearbox
Device short name	GBX
Product compatibility	BRS3 ILE (66 mm, 1 motor stacks) ILE (66 mm, 2 motor stacks) BCH2 (40 mm, 1 motor stacks) BCH2 (40 mm, 2 motor stacks)
Gearbox external diameter	40 mm
Reduction ratio	5:1

Complementary

Maximum torsional backlash	15 arc.min
Torsional rigidity	1 N.m/arcmin
Housing colour	Black
Housing material	Black anodized aluminium
Shaft material	C 45
Additional information	Lubricated for life
Service life in hours	30000 h at 100 rpm at 30 °C
Mounting position	Any position
Efficiency	98.0 %
Maximum radial force Fr	160 N at 100 rpm, force applied at mid-distance from output shaft during 30000 hour at 30 °C
Maximum axial force Fa	160 N at 100 rpm, during 30000 hour at 30°C
moment of inertia	0.027 kg.cm ²
Continuous output torque	14 N.m at 100 rpm at 30 °C
Maximum output torque	22 N.m at 100 rpm at 30 °C
Input diameter	8.0 mm
No load running torque	0.05 N.m
Reduction ratio	5
Compatibility code	GBX

Internal length 39.0 mm

Environment

Noise level 55 dB at 1 m, no-load

IP degree of protection Shaft output: IP54

ambient temperature for operation -25...90 °C

Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1 1

Package 1 Height 6.8 cm

Package 1 Width 7 cm

Package 1 Length 13.5 cm

Package 1 Weight 368 g

Unit Type of Package 2 S01

Number of Units in Package 2 10

Package 2 Height 15 cm

Package 2 Width 15 cm

Package 2 Length 40 cm

Package 2 Weight 4.725 kg

Logistical informations

Country of origin DE

Contractual warranty

Warranty 18 months



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1160
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	7c9e597c-8ccc-4daf-95fb-5d67fc70d561
REACH Regulation	REACH Declaration
PVC free	Yes


Use Again

Repack and remanufacture

Circularity Profile	No need of specific recycling operations
Take-back	No

Dimensions Drawings

Dimensions with Servo Motor Adaptation Kit



(1) GBK adaptation kit

(2) GBK adaptation kit related dimensions a1, c, Ø6, Ø7, Ø8 depend on the gearbox and servo motor combination

Ø8 shaft end adaptor in case motor shaft diameter is smaller than gearbox input coupling diameter

Values in mm

a2	a3	a4	a5	h	g	Ø1	Ø2	Ø3	Ø4	Ø5
39	26	23	2.5	11.2	3	40	26 h7	10 h7	M4 x 6	34

Values in in.

a2	a3	a4	a5	h	g	Ø1	Ø2	Ø3	Ø4	Ø5
1.54	1.02	0.90	0.10	0.44	0.11	1.57	1.02 h7	0.39 h7	M4 x 0.23	1.34