



Relays & Contactors > Electromechanical Relays



Relay & Contactor Type: **High Voltage Contactor**
Current Type: **DC**
Contact Arrangement: **1 Form A SPST-NO**
Contact Current Rating: **600 A**
Coil Voltage Rating: **12 VDC**

Features

Product Type Features

Relay & Contactor Type	High Voltage Contactor
------------------------	------------------------

Configuration Features

Relay Options	Not RF Rated, Power Switching
Contact Arrangement	1 Form A SPST-NO

Electrical Characteristics

Coil Resistance	18 Ω
Contact Switching Voltage (Max)	1800 VDC
Contact Current Rating	600 A
Coil Voltage Rating	12 VDC
Contact Voltage Rating	28 – 1800 VDC

Contact Features

Contact Material	Copper
------------------	--------

Termination Features

Main Termination & Connection Type	Screw Terminals
Coil Termination & Connection Type	Flying Leads

Mechanical Attachment

Product Mounting Feature Type	Flange with Screws
Product Mount Type	Panel Mount



Operation/Application

Current Type	DC
--------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts




TE Part # 1618002-7
EV200AAANA=RELAY, EV200 SPST-N

Customers Also Bought




TE Part #ZPF000000000039434
983-7SE 10-06 PN-L



TE Part #9-2176403-0
3550 5K1 1%



TE Part #1616068-4
K300A5C6=CONTACTOR



TE Part #41661
TAPER PIN



TE Part #1393766-2
R10-E1X2-S3.2K=R10




TE Part #8-1616982-7
K4001B5C2=CONTACTOR 400 A
SPST 28 VDC



TE Part #1616068-9
K300B5C5=CONTACTOR 300 AMP
SPST NO DB



TE Part #1-1616975-7
B309A=CONTACTOR 3PST NO 130
AMP



TE Part #66205-2
TAPER PIN 53 SERIES



TE Part #YDTS20F09-35PDV001
RECP ASSY

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1618002-4_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1618002-4_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1618002-4_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

5-1773450-5_sec7_EV500

English