




LED Spot MR16 Glass GU5.3 12V 2.6W (20W) 240lm 830 38°

Article number: 147103

BAI BaiSpot LED LV MR16 GU5.3 2.6W 3000K 38° All Glass Reflector 240lm (20W) 12V AC/DC 50x44mm LED-lamp

The so-called LED spots from the BaiSpot series are characterized by a much longer lifespan and significantly less energy consumption than their halogen predecessors. Due to the compact design, they are easily interchangeable. Spots are mainly used to provide directed light from the ceiling or wall. This glass version literally and figuratively has an extra beautiful appearance because the part through which the light shines is made entirely of glass. Ambient temperature range: -20°C to +45°C.



General ETIM properties

ETIM group	Lamps
ETIM class	LED-lamp/Multi-LED
Name	LED Spot MR16 Glass GU5.3 12V 2.6W (20W) 240lm 830 38°
Brand	Bailey
Productseries	BaiSpot LED LV GU5.3
Producttype	MR16 GU5.3 830 38D

ETIM specifications

Socket	GU5.3
Luminous flux [lm]	240 - 240
Nominal voltage [V]	12 - 12
Lamp power [W]	2.6 - 2.6
Colour temperature [K]	3000 - 3000
Diameter [mm]	50
Length [mm]	44
Dimmable	No
Lamp shape	Reflector
Beam angle [°]	38 - 38
Colour	White
Type of glass/cover	Prism
Lamp designation	MR16
Colour rendering index CRI	80-89
Voltage type	AC/DC
Filament lamp	No
Luminous intensity [cd]	335
Rated luminous flux according to IEC 62612 [lm]	240
Power factor	0.9
Lamp efficacy [lm/W]	93
Nominal current [mA]	230 - 230
Colour of light according to EN 12464-1	Warm white < 3300 K
Housing colour	Colourless
Average nominal lifetime [h]	15000
Degree of protection (IP)	IP20
Colour consistency (McAdam ellipse)	SDCM6
Min. number of switching cycles	7500
Weighted energy consumption in 1000 hours [kWh]	3
Remote operation possible	No
With movement sensor	No
With remote control	No
Photobiological safety according to EN 62471	RG1
Compatible with Apple HomeKit	No
Compatible with Google Assistant	No
Compatible with Amazon Alexa	No
IFTTT support available	No
Suitable for electronic ballast	No
Suitable for magnetic ballast	No
Dimming phase cut-off (trailing edge)	No
Dimming phase cut-on (leading edge)	No
Dimming Touch and Dim	No

Dimming Zigbee	No
Dimming Bluetooth	No
Dimming Wi-Fi	No
Energy efficiency class according to EU regulation 2019/2015	F
With twilight switch	No
Material of light bulb	Glass

Alternative articles



145083
LED Spot MR16 Glass GU5.3
12V 2.6W (20W) 240lm 830 36°



145060
LED Spot MR16 Glass GU5.3
12V 4.5W (35W) 460lm 830 38°

Complementary articles



146219
TOPO Little Transformer 12V AC
0-50W / LED 0-20W DIM



145683
TOPO Mini Transformer 12V AC
0-50W / LED 0-30W DIM