

product type designation

product description

Power Connecting Cable M12-180/M12-180

Flexible plug-in cable (4-wire), preferred length, pre-assembled with one 4-pin M12 male and one female connector (L-coded, 180° cable outlet)

Power connecting cable M12-180/M12-180 for the power supply of the terminal devices / network components: pre-assembled cable with M12 plug and M12 socket, L-coded, 4-pole, 2.0 m.



suitability for use

Cable for connecting the 24 V power supply to RF185C, RF186C, RF188C to IP65/67 degree of protection

cable designation

LIYY 4X1X1.5 BK

wire length

2 m

electrical data

operating voltage / RMS value

600 V

conductor cross section / of the power line

1.5 mm²

continuous current / of the power lines

16 A

mechanical data

number of electrical cores

4

type of electrical connection

M12-180

outer diameter

- of inner conductor
- of the wire insulation
- of cable sheath

1.6 mm
2.3 mm
7.7 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.3 mm

conductor class

5

material

- of the conductor
- of the wire insulation
- of cable sheath

CU, blank
PVC
PVC

product component / PE connection

No

marking / of cores

Color

color

- of the power line insulation
- of cable sheath

brown / white / blue / black
Black

bending radius

- with single bend / minimum permissible
- with multiple bends / minimum permissible
- with continuous bending

31 mm
62 mm
62 mm

number of bending cycles

2000000

tensile load / maximum

100 N

weight per length

97 kg/km

plug

type of plug interlock

screwed

design of plug-in connection

M12-180

connector coding

M12

connector coding / of the M12 circular connector

L-coded

ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> during operation during storage during transport during installation 	-20 ... +90 °C -30 ... +90 °C -30 ... +90 °C -20 ... +90 °C
fire behavior	Flame-resistant acc. to IEC 60332-1-2
chemical resistance	
<ul style="list-style-type: none"> to mineral oil to grease to water 	Oil resistant according to EN 50290-2-22 (VDE 0819), compound type TM55 (7x24h/90 °C) Conditional resistance Conditional resistance
radiological resistance / to UV radiation	resistant
protection class IP	IP65 / 67
product features, product functions, product components / general	
product feature	
<ul style="list-style-type: none"> halogen-free silicon-free 	No Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes
certificate of suitability	UL2238 E300110
<ul style="list-style-type: none"> EAC approval RoHS conformity 	Yes Yes
further information / internet links	
internet link	
<ul style="list-style-type: none"> to web page: selection aid TIA Selection Tool to website: Industrial communication to website: Industry Mall to website: Information and Download Center to website: Selection guide for cables and connectors to website: Image database to website: CAx-Download-Manager to website: Industry Online Support 	http://www.siemens.com/tia-selection-tool http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter https://sie.ag/2QdlxcP http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com

last modified:

11/9/2023 