





LOC		DIST		P		F		ZONE		LTR		REVISIONS		DATE		APPD	
CM	53											0	RELEASED PER PR CM 93-69	7-14-93	LS	RS	





SECTION B-B
SCALE 20:1



SECTION C-C
SCALE 20:1



SECTION A-A
SCALE 10:1



16.76	.660
2.79	.110
2.67	.105
2.41	.095
2.29	.090
2.24	.088
2.16	.085
2.06	.081
2.01	.079
1.93	.076
1.91	.075
1.57	.062
1.52	.060
1.40	.055
1.37	.054
1.02	.040
0.63	.025
0.38	.015
0.20	.008
0.13	.005
MM	IN

CONVERSION TABLE

METRIC

PRE-TIN	0.20 BRASS	1.52 MAX	0.2 - 0.5 mm ² (30-24 AWG)	794019-1
FINISH	MATERIAL	INSULATION DIAMETER	WIRE RANGE	PART NO
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.13 3 PLC DEC ± - ANGLES ± 0°30'		DR 7-14-93 L. SMITH	AMP AMP INCORPORATED Harrisburg, Pa. 17105	
		CHK 7-14-93 R. SWING		
		APPD 7-15-93 C. CASH		
SEE TABLE		APPD 7-15-93 C. CASH	NAME .062 SOCKET, LOOSE PIECE, COMMERCIAL PIN & SOCKET	
FINISH		APPLICATION SPEC	SIZE D	CAGE CODE 00779
SEE TABLE		WEIGHT -	SCALE 5:1	DRAWING NO 794019
				SHEET 1 OF 1