

QTP-OPTIMAL 1X18...40

QUICKTRONIC PROFESSIONAL OPTIMAL | ECG for FL and CFL, not dimmable



Areas of application

- Emergency lighting systems acc. to EN 50172 / DIN VDE 0108-100
- Industry
- Open-plan offices, corridors and storage rooms
- Public buildings
- Sports halls and factories
- Strip lighting
- Suitable for emergency lighting (DC operation)
- Modernization of existing systems

Product benefits

- Long lamp life
- No adverse effect from frequent on/off switching
- Automatic restart after lamp replacement
- Perfect lamp start for applications with motion sensors
- VDE/VDE EMC certified system
- Very high energy efficiency due to cut-off technology

Product features

- Supply voltage: 220...240 V
- Line voltage: 198...264 V
- Line frequency: 0 Hz | 50 Hz | 60 Hz
- Lamp start with optimum filament preheating
- Lifetime: up to 100,000 h (temperature at $T_c = 65$ °C, max. 10 % failure rate)
- Energy Efficiency Index EEI: A2 BAT
- Automatic shutdown of defective lamps and at end of life (EoL T.2)
- Safety: to EN 61347-2-3
- Lamp operation: to EN 60929

Product datasheet

Technical data

Electrical data

Input voltage AC	198...264 V
Nominal voltage	220...240 V
Mains frequency	50...60 Hz
Input voltage DC	176...276 V
Operating frequency	40...50 kHz
Max. no. of ECGs on circuit breaker 10 A	17 ¹⁾
Max. no. of ECGs on circuit breaker 16 A	28 ¹⁾
Inrush current	24 A

¹⁾ Type B

Light technical data

Starting time	1.5 s ¹⁾
---------------	---------------------

¹⁾ If there is a temporary interruption in the power supply (< 0.5 s), the lamp will start within 0.3 s

Dimensions & weight



Length	280.0 mm
Width	30.0 mm
Height	21.0 mm
Mounting hole spacing, length	270.0 mm
Product weight	180.00 g

Temperatures

Ambient temperature range	-20...+50 °C
---------------------------	--------------

Lifespan

ECG lifetime	100000 h ¹⁾
--------------	------------------------

Product datasheet

1) At tcase = 65°C at tc point / 10 % failure rate

Expected Lifetime

Product name	Lamp group				
QTP-OPTIMAL 1x18-40	HO 24 W	ECG ambient temperature [ta]	40	50	60
		Temperature at tc-point [°C]	50	60	70
		Lifetime [h]	100000	100000	80000
	HO 39 W	ECG ambient temperature [ta]	40	50	60
		Temperature at tc-point [°C]	55	60	70
		Lifetime [h]	100000	100000	80000
	L 18 W	ECG ambient temperature [ta]	40	50	60
		Temperature at tc-point [°C]	50	60	70
		Lifetime [h]	100000	100000	90000
	L 30 W	ECG ambient temperature [ta]	40	50	60
		Temperature at tc-point [°C]	50	60	70
		Lifetime [h]	100000	100000	80000
	L 32 W ES	ECG ambient temperature [ta]	40	50	60
		Temperature at tc-point [°C]	55	60	70
		Lifetime [h]	100000	100000	80000



Capabilities

Suitable for fixtures with prot. class	I / II
End of lamp life safety shutdown	EOL T.2








Certificates & standards

Approval marks – approval	EL / VDE / ENEC 10 / VDE-EMC
EEI – Energy Label	A2
Standards	Acc. to IEC 61347-2-3 / App. J/Acc. to EN 55015:2006 + A1:2007 + A2:2009/Acc. to IEC 61000-3-2/EN 61000-3-2/Acc. to IEC 61547
Protection class	I/II

Download Data

File	
	Addon Technical Information Frequent switching Quicktronic
	Product Datasheet ECG lifetime - QUICKTRONIC non DIM

Product datasheet

	Product Family Datasheet Familiendatenblatt QTP-Optimal
	Certificates ENEC QTP-Optimal
	Certificates EMC QTP-Optimal
	Certificates CE QTP-Optimal
	Certificates QTP-OPTIMAL VDE Certificate
	Certificates EAC certificate for Quicktronics QT
	Operating instructions EAC QTP-OPTIMAL

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4008321873743	QTP-OPTIMAL 1X18...40	Shipping carton box 20	312 mm x 166 mm x 98 mm	5.08 dm ³	3506.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.

QTP-OPTIMAL 1X18...40

QUICKTRONIC PROFESSIONAL OPTIMAL | ECG for FL and CFL, not dimmable

Product name	Lamp group	Nominal current	Nominal wattage + Power loss	Luminous flux at 35 °C	Number of lighting outlets
QTP-OPTIMAL 1x18-40	DULUX F 18 W	0.08 A	18.00 W	1050 lm	1
	DULUX F 24 W	0.12 A	25.00 W	1650 lm	1
	DULUX F 36 W	0.15 A	34.00 W	2700 lm	1
	DULUX L 18 W	0.09 A	19.00 W	1150 lm	1
	DULUX L 18 W XT	0.09 A	19.00 W	1150 lm	1
	DULUX L 24 W	0.12 A	27.00 W	1750 lm	1
	DULUX L 24 W XT	0.12 A	27.00 W	1750 lm	1
	DULUX L 36 W	0.16 A	35.00 W	2800 lm	1
	DULUX L 36 W XT	0.16 A	29.00 W	2800 lm	1
	DULUX L 40 W	0.20 A	44.00 W	3500 lm	1
	DULUX L 40 W CONSTANT	0.20 A	44.00 W	3500 lm	1
	HO 24 W	0.13 A	28.00 W	1750 lm	1
	HO 24 W CONSTANT	0.13 A	28.00 W	1900 lm	1
	HO 39 W	0.13 A	41.00 W	3100 lm	1
	HO 39 W CONSTANT	0.13 A	41.00 W	3400 lm	1
	L 15 W		13.50 W	950 lm	1
	L 16 W ES			1100 lm	1
	L 18 W	0.10 A	20.00 W	1350 lm	1

Product datasheet

Product name	Lamp group	Nominal current	Nominal wattage + Power loss	Luminous flux at 35 °C	Number of lighting outlets
	L 18 W U			1100 lm	1
	L 18 W XT	0.10 A	20.00 W	1350 lm	1
	L 18 W XXT	0.10 A	20.00 W	1350 lm	1
	L 30 W	0.15 A	36.00 W	2850 lm	1
	L 32 W ES	0.15 A	36.00 W	2500 lm	1
	L 36 W -1		36.00 W	3100 lm	1
	L 36 W	0.16 A	36.00 W	3200 lm	1
	L 36 W XT	0.16 A	36.00 W	3200 lm	1
	L 36 W XXT	0.16 A	36.00 W	3200 lm	1