

S3 CI HI SRC
EN ISO 20345:2011
35 to 48



Link-ESD

- Water-repellent full-grain leather
- PU/PU sole by BASF®
- ESD / Dissipative
- Polymer toe cap type B and midsole no metallic

- Urban sport-style safety shoe incorporating **MAXI-Soft Duo™** anti-fatigue technology designed for work stations that require standing for long periods (Upright or sustained activity)..
- Safety shoe protecting the electronic devices against electrostatic discharge phenomena. Electrostatic dissipative shoes ESD Environmental Class II tested according to **EN 61340-4-3** and **EN 61340-5-1**.
- Water-repellent full-grain leather upper and anti-abrasion heel. Black color. Fluorescent markings on the back of the heel.
- Upper lined in breathable **3D Surf** mesh with honeycomb structure to improve the peripheral ventilation of the foot, dries out rapidly.
- Padded tongue for good instep protection, combined with two side bellows to prevent any dirt from getting into the boots.
- Padded ergonomic collar in compact flexible foam, lined for extra comfort and better ankle and Achilles tendon protection.
- Lace up on five pairs of no metallic eyelets. Black laces 120 cm.
- Perforated insole for enhanced comfort : **MAXI-Soft Duo™** composed of a soft **BASF® Dynamic PU** midsole with heat sensitive memory foam and a maximum size **BASF® Elastopan insert** that improves weight distribution by reducing pressure points and absorbs and relieves body stress associated with a prolonged standing working position and when walking. Anatomical, breathable and fitted with the **Link ESDTM system**, an innovative and seamless, multi-contact, static electricity dissipater. (Patent pending).
- Ergonomic shoe, with broad synthetic polymer toe cap **Springtane-B™**. Impact resistance to 200 Joules. Minimum height after test $\geq 4\text{mm}$ in relation to the Type A toe cap in accordance with Standard 22568-2:2019.
- Stab-resistant structural insole and liner in **FleXtane™ By Jallatte ESD**, in compliance with standard 12568:2010, antistatic, **100% composite**. Sewn directly onto the upper and covering **100% of the foot for total protection**.
- Heel stiffener to reinforce the heel seat.
- BASF® PU / PU sole** with an urban sport design, linear profile and excellent slip resistance.



Slip resistance tests results EN Standard :
 EN ISO 20345 : 2011 **Requirement SRC** (SRA+SRB)

SRA Test ground : ceramic / lubricant : water and detergent
 On flat **0,62** (>0,32) – On the heel **0,48** (>0,28)

SRB Test ground steel/lubricant : glycerine
 On flat **0,23** (>0,18) – On the heel **0,19** (>0,13)



- Extremely light and flexible support base.
- Constant energy return over the entire surface.
- Reduced feeling of fatigue due to posture.
- Relief that facilitates the evacuation of fluids.



Weight	Gross weight (42) : 1376 g / Net weight (42) : 1160 g			
Size	35 to 39	40 to 42	43 to 45	46 to 48
Packaging	5 pairs	10 pairs		5 pairs
Box shoes (mm)	340 x 210 x 133		340 x 245 x 133	
Cartons (mm)	687 x 226 x 350	687 x 432 x 348	689 x 511 x 351	689 x 260 x 348