

# Magnetic label - PMM (EX50)R SR CUS - 1014331

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Magnetic label, can be ordered: By line, silver, labeled according to customer specifications, Mounting type: Magnetic adhesion, Lettering field: 15000 x 50 mm



## Key commercial data

Packing unit	1
GTIN	 4 046356 786355
Custom tariff number	39207380

## Technical data

### Dimensions

Length (b)	15000 mm
Width (a)	50 mm

### Ambient conditions

Ambient temperature (operation)	-30 °C ... 55 °C
---------------------------------	------------------

### General

Color	silver
Material	Magnetic tape
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	1
Number of individual labels per row	1
Marking mounting type	Magnetic adhesion

## Classifications

### eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199

## Magnetic label - PMM (EX50)R SR CUS - 1014331

### Classifications

#### eCl@ss

eCl@ss 5.0	27371301
eCl@ss 5.1	27371301
eCl@ss 6.0	27371301
eCl@ss 7.0	27371301
eCl@ss 8.0	27141137

#### ETIM

ETIM 3.0	EC000712
ETIM 4.0	EC002498
ETIM 5.0	EC001777

#### UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	43212107