




Connectors > Audio & Video Connectors > SDL Connectors



Connector & Housing Type: **Receptacle**  
Connector System: **Cable-to-Board**  
Number of Positions: **4**  
Centerline (Pitch): **1.27 mm [.05 in]**  
Connector & Contact Terminates To: **Printed Circuit Board**

Features

Product Type Features

Grounding Options	Panel Ground
Receptacle Configuration	Offset Flange
Connector & Housing Type	Receptacle
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	4
---------------------	---

Body Features

Shield Plating Material	Tin over Nickel
Shield Material	Brass

Contact Features

Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Phosphor Bronze
	50 µin
Contact Current Rating (Max)	1.5 A

Mechanical Attachment

PCB Mount Retention Type	Mounting Hole
Polarization Code	A



PCB Mount Retention	With
Connector Mounting Type	Board Mount

Housing Features

Housing Color	Black
Housing Material	Polyester GF
Mating Entry Location	Side
Centerline (Pitch)	1.27 mm[.05 in]

Usage Conditions

Operating Temperature Range	-20 – 80 °C[-4 – 176 °F]
-----------------------------	--------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5-1761186-1  
4 SDL SE O-S RCPT ASSY



TE Part # 1-1761182-1  
4 SDL SE RCPT ASSY

Customers Also Bought




TE Part #5-1761186-3  
8 SDL SE O-S RCPT ASSY



TE Part #292317-4  
STD USB TYPE B, R/A, T/H




TE Part #5-1761186-6  
16 SDL SE O-S RCPT ASSY



TE Part #5-1761185-1  
4 SDL SE GRND RCPT ASSY




TE Part #61761-2  
187 FASTON TAB TPBR



TE Part #1705951-1  
Modular Jack SE, 8/8, Gold flash



TE Part #5-1734857-5  
PCI EXP STRADDLE 36P BLK 30u"



TE Part #1-1761185-1  
4 SDL SE GRND RCPT ASSY



TE Part #292304-1  
STD USB TYPE B, R/A, T/H



TE Part #2246023-1  
Flex. Antenna Assembly

Documents

Product Drawings  
4 SDL SE O-S RCPT ASSY  
English



CAD Files

Customer View Model

ENG\_CVM\_1-1761186-1\_A2.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_1-1761186-1\_A2.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_1-1761186-1\_A2.2d\_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English