Pushing Performance
Since 1945

har-flex HD-Card Edge 80p THR PL1 200pcs



Image is for illustration purposes only. Please refer to product description.

Part number	15 04 080 2401 000
Specification	har-flex HD-Card Edge 80p THR PL1 200pcs
HARTING eCatalogue	https://harting.com/15040802401000

Identification

Category	Connectors
Series	har-flex®
Identification	HD-Card Edge
Element	Connector
Features	Termination method of hold downs: THR

Version

Termination method	Reflow soldering termination (SMT)
Connection type	Motherboard to daughtercard Mezzanine
Number of contacts	80
Pack contents	200 pieces on reel

Technical characteristics

Contact rows	2
Contact spacing (termination side)	0.8 mm
Contact spacing (mating side)	0.8 mm
Data rate	25 Gbit/s
Clearance distance	≥0.2 mm Backplane ≥0.53 mm Connector ≥0.1 mm Daughtercard
Creepage distance	≥0.2 mm Backplane ≥0.53 mm Connector ≥0.1 mm Daughtercard
Limiting temperature	-55 ... +125 °C

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Pushing Performance
Since 1945

Technical characteristics

Insertion force	≤55 N
Withdrawal force	≥16 N
Performance level	1
Mating cycles	≥200
Isolation group	IIIa (175 ≤ CTI < 400)
Moisture Sensitivity Level (MSL)	1 acc. to ECA/IPC/JEDEC J-STD-020D
Process Sensitivity Level (PSL)	R0 acc. to ECA/IPC/JEDEC J-STD-020D
Coplanarity of contacts	≤0.13 mm

Material properties

Material (insert)	Liquid crystal polymer (LCP)
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni Mating side Sn over Ni Termination side
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	1
Net weight	2.1 kg
Country of origin	China
European customs tariff number	85366990
GTIN	5713140205789
eCl@ss	27460201 PCB connector (board connector)
ETIM	EC002637
UNSPSC 24.0	39121415

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Pushing Performance
Since 1945

Data Transmission Protocols

har-flex HD-Card Edge Family Product Data Rate: 25Gbit/s				
Protocol	Serial Data Rate / Pair	Single Interface Short Channel	Double Interface Short Channel	Double Interface Long Channel
400GBASE-KR4	56 Gbit/s	Not recommended	Not recommended	Not recommended
100GBASE-KR4	25 Gbit/s	suitable	Not recommended	Not recommended
40GBASE-KR4	10 Gbit/s	suitable	suitable	suitable
Infiniband HDR	50 Gbit/s	Not recommended	Not recommended	Not recommended
Infiniband HDR	25.8 Gbit/s	Not recommended	Not recommended	Not recommended
Infiniband FDR	14 Gbit/s	suitable	suitable	suitable
PCIe Gen 4	16 Gbit/s	suitable	suitable	suitable
PCIe Gen 3	8 Gbit/s	suitable	suitable	suitable
PCIe Gen 2	5 Gbit/s	suitable	suitable	suitable
USB 3.1	5 Gbit/s	suitable	suitable	suitable
USB 3.0	5 Gbit/s	suitable	suitable	suitable
Hypertransport 3	5.2 Gbit/s	suitable	suitable	suitable
SATA 3.2	16 Gbit/s	suitable	suitable	suitable
SAS 4.0	22.5 Gbit/s	Not recommended	Not recommended	Not recommended
SAS 3.0	12 Gbit/s	suitable	suitable	suitable
SAS 2.0	6 Gbit/s	suitable	suitable	suitable

The protocol recommendations are based on a set of defined channels. For more information please refer to the reference channel descriptions:
https://d33y5j6752j001.cloudfront.net/asset/201312468866/document_ifd9i1f1bd01t6mk6dr9s45u2u

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com