

Product datasheet

Specifications



Rack PDU, Switched, 2U, 30A, 208V, (16)C13

AP7911B

EAN Code: 0731304331605

Main

Colour	Black
Product or component type	PDU
PDU type	Switched
Cord length	3.65 m
Number of cables	1
Provided equipment	Documentation CD Installation guide Rack mounting brackets

Complementary

Input Voltage	200 V 208 V 230 V
Height	89 mm
Width	445 mm
Output Voltage	208 V
Depth	254 mm
Product weight	6.32 kg
Mounting location	Front Rear
Mounting preference	No preference
Input Plug Type	NEMA L6-30P
mounting mode	Rack-mounted
Rack units	2U
Mounting position	Horizontal
[In] rated current	24 A
permissible voltage	200...240 V
Input current limits	30 A
Load capacity	4992 VA
Network frequency	50/60 Hz
Outlet type and quantity	16 IEC 60320 C13

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product certifications	cUL listed CSA Industry Canada PSE UL listed
Standards	FCC part 15 class A ICES-003 UL 60950
Ambient air temperature for operation	0...45 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	0...95 %
Storage altitude	0...15240 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14.6 cm
Package 1 Width	51.4 cm
Package 1 Length	51.4 cm
Package 1 Weight	8.36 kg

Logistical informations

Country of origin	IN
-------------------	----

Contractual warranty

Warranty (in months)	24
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	2 005 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	46 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.2 kg CO2 eq.
Carbon footprint of the installation phase [A5]	1 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	1 954 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	3 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Free of Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	71
End of life manual availability	End of Life Information
Removable battery	Yes
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative

