


Product datasheet

Specifications



servo motor SH3 040 0,39Nm,no
key,multi,brake,90°conn,IP54/
IP65,9k RPM

SH30402P07F2000

EAN Code: 3606485467689

Main

Range compatibility	PacDrive 3
Device short name	SH3
Product or component type	Servo motor

Complementary

Maximum mechanical speed	9000 rpm
[Us] rated supply voltage	115...480 V
Network number of phases	Three phase
Continuous stall current	1.5 A
Continuous stall torque	0.39 N.m at 115...480 V three phase
Continuous power	290 W
Peak stall torque	1.5 N.m at 480 V three phase
Nominal output power	152 W at 115 V single phase 152 W at 230 V single phase 275 W at 400 V three phase 289 W at 480 V three phase
Nominal torque	0.292 N.m at 115 V single phase 0.292 N.m at 230 V single phase 0.31 N.m at 400 V three phase 0.31 N.m at 480 V three phase
Nominal speed	4000 rpm at 115 V single phase 4000 rpm at 230 V single phase 9000 rpm at 400 V three phase 9000 rpm at 480 V three phase
Maximum current Irms	7.2 A
Shaft end	Smooth shaft
Shaft diameter	8 mm
Shaft length	25 mm
IP degree of protection	IP54 shaft bushing without shaft seal ring: conforming to IEC 60034-5 IP65 motor: conforming to IEC 60034-5 IP65 shaft bushing: conforming to IEC 60034-5
Encoder type	Absolute multiturn SinCos Hiperface
Speed feedback resolution	16 periods
Holding brake	With
Holding torque	0.4 N.m
Mounting support	International standard flange
Motor flange size	40 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Electrical connection	Straight connector
Torque constant	0.26 N.m/A at 120 °C
Back emf constant	18 V/krpm at 20 °C
Number of motor poles	5.0
Rotor inertia	0.0588 kg.cm²
Stator resistance	11.6 Ohm
Stator inductance	6.4 mH
Type of cooling	Natural convection
Length	119.4 mm
Centring collar diameter	30 mm
Centring collar depth	2.5 mm
Number of mounting holes	4
Mounting holes diameter	4.5 mm
Circle diameter of the mounting holes	46 mm
Net weight	0.8 kg
Sizing reference	SH30402P
Network number of phases	3
Temperature copper hot	120 °C
Electrical connection	rotatable right angled connector
Output current 3s peak	7.2 A
Inertia	0.017 kg.cm² of brake 0.042 kg.cm² of motor

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.900 cm
Package 1 Width	17.000 cm
Package 1 Length	24.600 cm
Package 1 Weight	990.000 g

Contractual warranty

Warranty (in months)	18
----------------------	----

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

 Environmental footprint	
Total lifecycle Carbon footprint	640
Environmental Disclosure	Product Environmental Profile

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ead0850d-370a-47c5-8cf7-1d93c2c974a4
REACH Regulation	REACH Declaration
PVC free	Yes

Use Longer

 Lifetime extension	
Repair	No

Use Again

 Repack and remanufacture	
End of life manual availability	No need of specific recycling operations
Take-back	No