

# Product datasheet

Specifications

Schneider Electric C200N3FM

Picture

Circuit breaker frame,  
ComPacT NS2000N, 50kA at  
415VAC, 2000A, 3P, fixed,  
manually operated, without  
control unit

C200N3FM

EAN Code: 3606482098619

## Main

Range	ComPacT
Range of product	ComPacT NS1600b...3200 new generation
Product or component type	Basic frame
Device application	Distribution
Number of poles	3P
[In] rated current	2000 A at 50 °C
[Ue] rated operational voltage	690 V AC 50/60 Hz
Network type	AC
Network frequency	50/60 Hz
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Utilisation category	Category B
Breaking capacity	85 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 70 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 65 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 65 kA Icu at 500/525 V AC 50/60 Hz conforming to IEC 60947-2 65 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2
Breaking capacity code	N 70 kA 415 V AC
Control type	Manually operated
Mounting mode	Fixed

## Complementary

[Ui] rated insulation voltage	800 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-2
[Ics] rated service breaking capacity	65 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 52 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 65 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 65 kA at 500/525 V AC 50/60 Hz conforming to IEC 60947-2 65 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2
[Icw] rated short-time withstand current	32 kA 3 s conforming to IEC 60947-2
Integral instant protection	130 kA
Mechanical durability	5000 cycles conforming to IEC 60947-2
Electrical durability	1000 cycles 690 V AC 50/60 Hz In conforming to IEC 60947-2 2000 cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-2 2000 cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2 3000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2

Power losses	84 W
Mounting support	Backplate
Connection pitch	70 mm
Protection type	Without protection
Height (H)	360 mm
Width (W)	420 mm
Depth (D)	160 mm

## Environment

Standards	IEC 60947-2
Product certifications	IECEE CB Scheme
Overvoltage category	III
Electrical shock protection class	Class II on front face
Pollution degree	3 conforming to IEC 60947
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to EN 50102
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	43.0 cm
Package 1 Width	60.0 cm
Package 1 Length	80.0 cm
Package 1 Weight	41.994 kg

## Logistical informations

Country of origin	FR
-------------------	----

## Contractual warranty

Warranty (in months)	18
----------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Use Better



#### Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	228b8554-bb98-43c5-8445-d118744be8d8
EU RoHS Directive	<a href="#">Compliant By Exemption</a>
REACH Regulation	<a href="#">Reference contains Substances of Very High Concern above the threshold</a>

### Use Longer




#### Lifetime extension

Repair	No
--------	----

### Use Again



#### Repack and remanufacture

Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins