

Identification Systems

Report Generating Accessories

3-349-475-03
7/10.11

B3261 Barcode Scanner

- Sampling rate: 256 scans per second
- PUZZLE SOLVER™ technology

Z502F, Z720A and Z751A Barcode Scanners

- Scanning distances of up to 20 cm
- Green Spot technology

Z721D Barcode Printer

- High speed device
- Can be integrated into networks

Z751G RFID Read / Write

- Combined read and write system for 13.56 MHz transponders
- RS 232 interface

Z751E RFID Read / Write

- Combined read and write system for 13.56 MHz transponders
- USB-HID interface

Z751D RFID Reader / RFID Scanner

- Compact handheld device for reading 125 kHz transponders
- USB-HID interface



Application

Barcode and RFID identification systems are used to mark and identify tools and equipment.

The scanning devices are exclusively matched to the interfaces included with SECUTEST, PROFITEST, MINITEST, SECUSTAR and SECULIFE test instruments. They forward the scanned code to the respective test device in order to be able to allocate measured values and test results to the device under test in an unequivocal fashion.

ID numbers can be written to RFID tags with the SCANBASE RFID devices (Z751G and E). ID numbers can be printed onto barcode labels with the barcode printer and a PC.

Features

B3261 Barcode Scanner

The barcode scanner is a complete, all-in-one solution with outstanding reading performance (256 scans per second) and reliability. The B3261 is equipped with an RS-232 port.

Z720A and Z751A Barcode Scanners

These devices are based upon the concept of an instinctive scanning distance and provide best possible reading performance at distances of up to 20 cm. Green Spot technology projects "good-read" indication directly onto the code. The Z720A is equipped with an RS 232 port, and the Z751A with a USB port.

Z721D Barcode Printer

High performance, fast, PC compatible labeling system. Prints especially high quality, durable labels. The device is particularly well suited for printing resilient barcode labels.

Z751G SCANBASE RFID: RFID Reader / Writer

Compact reading and writing device with RS 232 port for programming and reading 13.56 MHz transponders in accordance with ISO15693.

Z751E SCANBASE RFID: RFID Reader / Writer

Compact reading and writing device with USB port for programming and reading 13.56 MHz transponders in accordance with ISO15693.

Z751D SCANBASE RFID: RFID Reader / RFID Scanner

Flexible, universal reading module for 125 kHz transponders. The device is equipped with a USB-HID interface and an ergonomically shaped housing.

Applicable Regulations and Standards

DIN EN 61326
VDE 0843, part 20

Electrical equipment for control technology and laboratory use – EMC requirements

Identification Systems

Report Generating Accessories


Device Overview

							
Designation	Barcode Scanner	Barcode Scanner			RFID Reader/Scanner	RFID Read/Write	RFID Read/Write
Type Feature Article no.	B3261 GTZ3261000R0001	Z720A Z720A	Z502F Z502F	Z751A Z751A	SCANBASE RFID Z751D ²⁾	SCANBASE RFID Z751E ²⁾	SCANBASE RFID Z751G ^{2) 3)}
Connection interfaces	RS232	RS232	RS232	USB	USB-HID	USB-HID	RS232
Connection cable (2 m)	stright	stright	coiled	stright	stright	stright	stright
Frequency	—				125 kHz	13.56 MHz	
Readable codes (selection), RFID tags	Code 39, code 128, EAN 13 (12 digits) ¹⁾				HITAG1, 2, S, Q5, Titan, Atmel5577, EM-4XXX	ISO15693, Z751R, Z751S, Z751T	
Scanning distance	Approx. 50 mm	Max. 210 mm			Approx. 50 mm	Approx. 30 mm	Approx. 30 mm
Power supply	Via interface				Via interface		
Operating temperature	0 °C ... 55 °C				–10 °C ... 55 °C		
Dimensions	164 x 77.5 x 63 mm	195 x 70 x 66 mm			240 x 120 x 35 mm		
Usable for following devices and product ranges	SECUTEST PSI, SI, SI+, SECUSTORE PROFITEST (P)SI-BC, PROFITEST 204 PROFITEST M ..., MINITEST MASTER, MINITEST 3P MASTER, SECUTEST SII+, SECUTEST SIII+, SECUTEST 3PL, SECULIFE ST			SECUSTAR FM, SECULIFE SB	SECUSTAR FM, SECULIFE SB		MINITEST MASTER, MINITEST 3P MASTER, SECUTEST SII+, SECUTEST SIII+, SECUTEST 3PL, SECULIFE ST, PROFITEST 204 PROFITEST M ..., SECUSTORE

¹⁾ Z720A and Z751A have the appropriate scanning width to be programmed to the EAN 128 barcode.

²⁾ In order to program the RFID tags, the respective RFID scanner/programmer must be connected to the PC by using the software which is available on the attached CD ROM.






³⁾ Please note: Z751GA requires a special RS232 cable and power supply unit which are both available from our Customer Service Center. The contact address is given on the last page.

	
Designation	Barcode Printer
Type	Z721D
Feature Article no.	Z721D
Connection interfaces	To the PC: USB, serial
Text entry	Via PC keyboard
Fonts	All of the computer's true type fonts
Font sizes	1.2 to 27 mm
Label tape	TZ, AL, HG
Label tape width	6, 9, 12, 18, 24, 36 mm (TZ/HG), 24 mm (AL)
Print resolution	360 dpi
Printing speed	Up to 80 mm per second
Power supply	Power pack
Weight	1.6 kg
Dimensions	116 x 192 x 140 mm

Identification Systems

Report Generating Accessories

Accessories Overview

				No photo		
Designation	RFID Tag				Label Tape Cartridge	
Type	Z751R	Z751S	Z751T	ZxxxX	Z722D	Z722E
Feature Article no.	Z751R	Z751S	Z751T	ZxxxX	Z722D	Z722E
Usable for following devices	Z751D, Z751E, Z751G				Z721D	
Frequency	13.56 MHz			125 kHz	—	
Chip	ICODE SLI with 1 kBit data memory				—	
Writing cycles	100,000				—	
Reading cycles	Unlimited				—	
Material	ABS				—	
Temperature range	-20° to +60° C				—	
Standard	ISO 15693			HITAG1, 2, S, Q5, Titan, Atmel5577, EM-4XXX	—	
Type	Dia. approx. 22 mm, self-adhesive (the photos show the front, as well as the adhesive back)	Approx. 30 x 2 mm with 3 mm hole	Pigeon ring, dia. approx. 10 mm	Upon request	Cartridge	
Quantity per package	500 pieces		250 pieces	1000 pieces	1 set of labels includes the following label tape cartridges: 3 x 24 mm wide, 1 x 18 mm wide, 1 x 9 mm wide, length: 8 m each	1 set of labels includes the following label tape cartridges: 5 x 18 mm wide, length: 8 m each

Identification Systems

Report Generating Accessories

Order Information

Description	Type	Article Number
Barcode Scanners		
Barcode scanner for RS 232 connection (LED sensor)	B3261	GTZ3261000R0001
Barcode scanner for RS 232 connection (laser sensor), variable barcode length, enhanced reading accuracy	Z720A	Z720A
Barcode scanner for RS 232 connection (laser sensor), variable barcode length, enhanced reading accuracy, with coil-cable	Z502F	Z502F
Barcode scanner for USB connection	Z751A	Z751A
Barcode Printer		
Barcode and label printer including software, for USB and RS232 connection to the PC	Z721D	Z721D
Accessories		
Label set for Z721D barcode and label printer (quantity x width: 3 x 24, 1 x 18, 1 x 9 mm, length: 8 m each)	Z722D	Z722D
Label set for Z721D barcode and label printer (qty. x width: 5 x 18 mm, 8 m long each)	Z722E	Z722E
RFID Readers / Scanners		
RFID reader / RFID scanner for USB connection (frequency: 125 kHz)	SCANBASE RFID	Z751D
RFID read/write for USB connection (frequency: 13.56 MHz)	SCANBASE RFID	Z751E
RFID read/write for RS 232 connection (13.56 MHz)	SCANBASE RFID	Z751G
Accessories		
RFID tags per ISO 15693, dia. approx. 22 mm, self-adhesive, 500 pcs.	Z751R	Z751R
RFID tags per ISO 15693, dia. approx. 30 x 2 mm with 3 mm hole, 500 pcs.	Z751S	Z751S
RFID tags per ISO 15693, pigeon ring, dia. approx. 10 mm, 250 pcs.	Z751T	Z751T
RFID tag (125 kHz), shape as requested, 1000 pcs.	ZxxxX	ZxxxX

For additional information regarding accessories please refer to:

- The data sheet for the respective device or our Measuring Instruments and Testers catalogue.
- www.gossenmetrawatt.com

Edited in Germany • Subject to change without notice • PDF version available on the Internet



GMC-I Messtechnik GmbH
Südwestpark 15
90449 Nürnberg • Germany

Phone +49 911 8602-111
Fax +49 911 8602-777
E-Mail info@gossenmetrawatt.com
www.gossenmetrawatt.com