


KEMET Part Number: ALS70A473QS200
(A390UV473M200A)

ALS70, Aluminum Electrolytic, 47,000 uF, 20%, 200 VDC, -40/+85°C



General Information

Supplier:	KEMET
Series:	ALS70
Dielectric:	Aluminum Electrolytic
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
AEC-Q200:	No
Notes:	Dimensions D And L Include Sleaving. MS (MxH) = M12x16. Mounting Clip (Sold Separately): PYC6045

Dimensions

D	90mm +/-1mm
L	194mm +/-2mm
T	5.5mm +/-0.5mm
S	31.8mm +/-0.5mm
DT	13mm +/-0.5mm
LT	198mm +/-1mm
TD	10mm MIN
V	25mm NOM
Z	10mm NOM

Packaging Specifications

Weight:	1.8 kg
Sleaving:	Yes
Packaging:	Tray

Specifications

Capacitance:	47,000 uF
Capacitance Tolerance:	20%
Voltage DC:	200 VDC, 230 VDC (Surge)
Temperature Range:	-40/+85°C
Rated Temperature:	85°C
Life:	20000 Hrs (Rated Voltage And Ripple Current At 85C), 40000 Hrs (Rated Voltage At 85C)
Resistance:	11 mOhms (100Hz 20C), 10 mOhms (10kHz 20C)
Ripple Current:	31.9 Amps (100Hz 85C), 37 Amps (10 kHz 85C)
Leakage Current:	6000 uA