



QMFZ2.E219300 Plastics - Component

For enhanced search functionality, please visit UL's [iQ™ Family of Databases](#).
Click on a product designation for complete information.

[Page Bottom](#)

Plastics - Component

[See General Information for Plastics - Component](#)

EUROFOAM SRL
VIA C COLOMBO 12
20020 LAINATE, MI ITALY

E219300

| | | | | | | | | | | | |
|---|-------|------|-------|---|---|-------|------|-----|---|---|---|
| | | | | | | | | | H | D | |
| | | Min. | | H | H | R T I | | | V | 4 | C |
| | | Thk | Flame | W | A | Elec | Mech | | T | 9 | T |
| Material Dsg | Color | mm | Class | I | I | | Imp | Str | R | 5 | I |
| Neoprene "Chlorinated Butadiene" Rubber (CBR), furnished as sheets. | | | | | | | | | | | |
| POR 303/B UL (a) | NC | 2.0 | HF-1 | - | - | 50 | 50 | 50 | - | - | - |
| | | 10 | V-0 | - | - | 50 | 50 | 50 | | | |
| | | 13 | HF-1 | - | - | 50 | 50 | 50 | | | |
| Polyethylene (PE), furnished as sheets. | | | | | | | | | | | |
| PE 30/UL (b) | GY | 2.0 | HF-1 | - | - | 50 | 50 | 50 | - | - | - |
| | | 13 | HF-1 | - | - | 50 | 50 | 50 | | | |

(a) - Density range from 0.115 to 0.165 g/cc

(b) - Density range from 0.023 to 0.028g/cc

Marking: Company name and material designation on container, wrapper or finished part.

Last Updated on 2015-01-09

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

© 2016 UL LLC

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2016 UL LLC".