



Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Grommet Seal**

Operating Temperature Range: **-40 – 135 °C [-40 – 275 °F]**

Primary Product Color: **Black**

Operating Temperature (Max): **135 °C [275 °F]**

Features

Product Type Features

Connector Seal & Plug Type	Grommet Seal
----------------------------	--------------

Body Features

Primary Product Color	Black
-----------------------	-------

Usage Conditions

Operating Temperature Range	-40 – 135 °C[-40 – 275 °F]
Operating Temperature (Max)	135 °C[275 °F]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1437709-4
106015/106016=TERMINAL FEM. CR



TE Part # 5-1437710-6
NP1TA-00R2XX=CONN. 2W MALE WAT




TE Part # 2-1437712-2
MP1NA-1008XX=CONN. 8W FEMA BLK


Customers Also Bought



TE Part #1745083-1
3 POS. PLUG ASSY AMP SUPERSEAL 1.5 SRS



TE Part #967610-1
MPO EINZELLEITDICHT



TE Part #8134334001
CGPT-39/13-0-SP



TE Part #2-1437712-5
NP1WA-0002XX=CONN. 2W FEMA BLK




TE Part #1-1437709-1
106009/106010=TERMINAL MALE CR




TE Part #324061
TERMINAL,SOLIS R 8 8



TE Part #1879980-1
MINI SUPERSEAL CONNECTOR



TE Part #166309-2
MOD-5 REC.CONTACT



Documents

Product Drawings

106099=GROMMET BLACK

English

106099=GROMMET BLACK

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1437713-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1437713-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1437713-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Datasheet

English