

63698-1 ✓ ACTIVE


TE Internal #: 63698-1

Closed Ring Tongue Terminal, 16 – 12 AWG, #8 / M4 Stud, 4.39 mm [.172 in] Stud Diameter, Open Barrel, Straight, Tin Plating, Uninsulated

[View on TE.com >](#)



Terminals & Splices > Ring Terminals



Ring Terminal Product Type: **Closed Ring Tongue Terminal**

Wire Size: **2582 – 6529 CMA**

Stud Size: **#8, M4**

## Features

### Product Type Features

Shape Description	Anti-Rotational/Grounding
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#8, M4
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

### Contact Features

Contact Base Material	Brass
Barrel Type	Open
Terminal Orientation	Straight
Terminal Plating Material	Tin
Contact Underplating Material	Nickel

### Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

### Dimensions

.13 in
--------

Wire Size	2582 – 6529 CMA
Stud Diameter	4.39 mm [.172 in]
Tongue Thickness	.76 mm [.03 in]
Product Length	19.56 mm [.77 in]
Barrel Inside Diameter	2.03 mm, 3.93 mm [.08 in] [.155 in]
Compatible Insulation Diameter (Max)	4.32 mm [.17 in]
Compatible Insulation Diameter Range	3.3 – 4.32 mm [.13 – .17 in]

### Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C [-40 – 230 °F]

### Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

### Industry Standards

Government Qualified Terminal	No
-------------------------------	----

### Packaging Features

Packaging Quantity	6000
Packaging Method	Strip/Reel

### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as

EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 7-2150653-7  
OCEAN\_2.0\_SPARE\_PART\_KIT-140F220O



TE Part # 2150653-1  
OCEAN\_2.0\_APPLICATOR-E-140F220O-REM



TE Part # 2150653-2  
OCEAN\_2.0\_APPLICATOR-E-140F220OA-REA

## Customers Also Bought



TE Part #2-34854-1  
TERMINAL,PG R 12-10 10



TE Part #2-34855-1  
TERMINAL,PG R 12-10 1 4



TE Part #42742-1  
250 FASTON FLAG REC 18-12 AWG BR




TE Part #42742-2  
250 FASTON FLAG REC 18-12 AWG TPBR



TE Part #42745-2  
PIN 090 FLAG RECEPTACLE 20-14 AWG TPPHBZ




TE Part #61969-1  
187 FASTON REC 20-16 AWG TPBR



TE Part #154718-3  
PL 250 REC 0.7-2.0 MM2 0.406 TPBR



TE Part #350434-1  
15P UMNL PIN HDR ASSY NATL



TE Part #640204-1  
RING .164 (4.17 MM) 22-18 AWG TPST



TE Part #737440-2  
250 FASTON REC 17-14 AWG TPBR

## Documents

### Product Drawings

[RING,M4, DIA 4.39,16-12,TPBR](#)

English

---

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_63698-1\\_C\\_c-63698-1-c.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_63698-1\\_C\\_c-63698-1-c.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_63698-1\\_C\\_c-63698-1-c.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Product Specifications

[Engineering Report](#)

English