



Part Number : [732870313](#)

Product Description : 2.92mm Attenuator, Plug to Jack, Straight, 40 GHz, 0.5 Watt, 6 dB, with Hex

Series Number : 73287

Status : Active

Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings

[732870313_sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73287
Description	2.92mm Attenuator, Plug to Jack, Straight, 40 GHz, 0.5 Watt, 6 dB, with Hex
Application	RF
Keyword	Attenuators, Attenuator
Product Name	2.92mm,Attenuator
Style	Fixed Coaxial Attenuator
Type	Subminiature
UPC	198282629184

Electrical

Average Power Max (Watts)	0.5
Attenuation Level (dB)	6
Frequency	40 GHz
Impedance	50Ω
VSWR (max)	1.40:1

Physical

Body Style	With Hex
Cable Attachment	N/A
Gender	Plug/Jack
Keying to Mating Part	N/A
Orientation	Straight
Packaging Type	Bag
Panel Mount	No

Panel Mount Method	N/A
PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	N/A

This document was generated on Oct 02, 2025