



HT-SCE

TE Internal #: 531520-000

Ladder, High Temperature, 2:1, White, 50.8 mm [2 in] Length, 38.1 mm [1.5 in] Expanded Inside, Shrinks To 19.1 mm [.75 in], HT-SCE, Printable Tubing

[View on TE.com >](#)

Identification & Labeling > Printable Tubing > HT-SCE High Temperature Sleeves



Printable Tubing Type: **Ladder**

Printable Tubing Grade: **High Temperature**

Shrink Ratio: **2:1**

Primary Product Color: **White**

Product Length: **50.8 mm [2 in]**

[All HT-SCE High Temperature Sleeves \(51\)](#)

Features

Product Type Features

Printable Tubing Type	Ladder
Printable Tubing Grade	High Temperature

Body Features

Shrink Ratio	2:1
Primary Product Color	White

Dimensions

Product Length	50.8 mm[2 in]
Expanded Inside Diameter (Min)	38.1 mm[1.5 in]
Recovered Inside Diameter (Max)	19.1 mm[.75 in]
Compatible Cable Diameter Range	19 – 30.48 mm[.75 – 1.2 in]

Usage Conditions

Operating Temperature Range	-55 – 225 °C[-67 – 437 °F]
-----------------------------	----------------------------

Printer/Label Features

Printer Technology	Thermal Transfer
--------------------	------------------

Packaging Features

--	--



Packaging Quantity	1000
--------------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186501-1
T3212-SWARE-PRINTER



TE Part # 754073-000
TMS-RJS-RIBBON-4HT



TE Part # 1-2186500-1
T3212-PRINTER



TE Part # 1-2186502-1
T3224-PRINTER



TE Part # 1-2186503-1
T3224-SWARE-PRINTER

Also in the Series | HT-SCE



Printable Tubing(16)

Customers Also Bought



TE Part #1717677-1
CAP ASSY,12P,BRACKET REVERSE
TYPE,ATAC C



TE Part #51864-3
TERMINAL,PIDG R 16-14 6



TE Part #321889
SOLIS R HT 22-16COMM22-18MIL 6



TE Part #2187461-1
SW PIR HDR BP, 100OHM, 9X6SP DEW



TE Part #6162-283-0877
CONT PIN ASSY



TE Part #E07443-000
HW-508254-5-9



TE Part #2187194-1
SW PIR RECT, 100OHM, 9X6SP



TE Part #6036230001
HT-SCE-1K-1/2-2.0-9



TE Part #YDTS24T25-35SNV001
RECP ASSY



TE Part #2804-6-1200
INS PIN ASSY



Documents

Datasheets & Catalog Pages

[HT-SCE High Temperature Heat Shrink Identification System](#)

English

Product Specifications

[IDENTIFICATION PRINTER PRODUCT RIBBON MATRIX](#)

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English