

Guided drive DGRC-GF-25-50-PA

Part number: 8218209

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Distance from centre of gravity of load to yoke plate xs	50 mm
Stroke	50 mm
Piston diameter	25 mm
Operating mode, drive unit	Yoke
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	Any
Guide	Plain-bearing guide
Design	Guidance
Position detection	Via proximity switch
Symbol	00991737
Protection against torque/guide	Guide rod with yoke
Operating pressure	0.15 MPa ... 1 MPa
Operating pressure	1.5 bar ... 10 bar
Max. speed	0.8 m/s
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Ambient temperature	-10 °C ... 60 °C
Impact energy in end positions	0.3 J
Max. force Fy	663 N
Max. force Fy static	663 N
Max. force Fz	663 N
Max. force Fz static	663 N
Max. moment Mx	21.22 Nm
Max. torque Mx static	21.22 Nm
Max. moment My	9.28 Nm
Max. torque My static	9.28 Nm
Max. moment Mz	9.28 Nm
Max. torque Mz static	9.28 Nm
Max. permissible torque load Mx as a function of stroke	3.17 Nm
Max. effective load dependent upon stroke at defined distance xs	64.1 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	247 N

Feature	Value
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	295 N
Torsional backlash	0.045 deg
Moving mass	336.8 g
Product weight	697.6 g
Basic weight for 0 mm stroke	360.8 g
Centre of gravity of moving mass as a function of stroke	37.3 mm
Pneumatic connection	G1/8
Note on materials	RoHS compliant
Material cover	Wrought aluminium alloy
Material seals	NBR
Material dynamic seals	TPE-U(PU)
Material end plate	Anodised wrought aluminium alloy
Material guide rod	High-alloy steel
Material housing	Anodised wrought aluminium alloy
Material piston rod	High-alloy steel