


DOC NO	ISSUE	REVISION	PRODUCT REF.	DATE	QUALITY PLAN
QF/RD/05	01	00	FAR0308	10.10.14	
<b>TECHNICAL SPECIFICATIONS</b>				<b>SIGNATURE</b>	
				<b>PRESIDENT (TECHNICAL)</b>	

## WORK POSITIONING LANYARD (FAR0308)



### DESIGN

- Rope ends spliced and covered with polyethylene protective sleeve.
- Abrasion resistant thimbles provided within loops.
- Adjustable length upto 2 meters maximum.
- Adjustment by use of ring type adjuster.
- Karabiners (112) provide at both end for attachment.

### ROPE

- Rope used comply to ISO 1140.
- Ø14 mm three strand polyamide rope.
- Black & Red Tracer in the rope to indicate degradation of material.
- Breaking strength minimum 25 kN.

### RING TYPE ADJUSTER

- Material : Forged alloy steel rope adjuster ring.
- Plating : Zinc plated.
- Finish : Deburred & Polished.

### VITAL TEST COMPLIANCE

- Static Strength : 15 kN for 3 Minutes.
- Dynamic strength : Free fall from 1 meter height with a test mass of 100 kg.

### WEIGHT

- 2.0 Meter : 770 gm ±10 gm.

