

Eaton 222867

Catalog Number: 222867

Eaton Moeller® series T3 Main switch, T3, 32 A, surface mounting, 3 contact unit(s), 3 pole, 2 N/O, Emergency switching off function, With red rotary handle and yellow locking ring

General specifications

Product Name	Catalog Number
Eaton Moeller® series T3 Main switch	222867
EAN	Product Length/Depth
4015082228675	206 mm
Product Height	Product Width
135 mm	187 mm
Product Weight	Certifications
0.585 kg	IEC/EN 60947
	CE
	UL
	CSA-C22.2 No. 60947-4-1-14
	CSA-C22.2 No. 94
	IEC/EN 60947-3
	UL Category Control No.: NLRV
	CSA Class No.: 3211-07
	CSA File No.: 012528
	UL 60947-4-1
	VDE 0660
	IEC/EN 60204
	CSA
	UL File No.: E36332

Catalog Notes

Rated Short-time Withstand Current
(Icw) for a time of 1 second

Product specifications

Product Category

Main switch

Features

Version as maintenance-/service switch

Version as main switch

Version as emergency stop installation

Actuator color

Red

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

UV resistance only in connection with protective shield.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be

Resources

Brochures

Brochure - T Rotary Cam switch and P Switch-disconnector

Catalogs

P Switch-disconnectors and T Rotary cam switches catalogue
CA042001EN

Declarations of conformity

DA-DC-00004923.pdf

DA-DC-00004894.pdf

Drawings

eaton-rotary-switches-padlock-t0-main-switch-dimensions.eps

eaton-rotary-switches-surface-mounting-t3-main-switch-dimensions-002.eps

eaton-rotary-switches-dimensions-t3-main-switch-dimensions.eps

eaton-general-totally-insulated-t0-main-switch-symbol.eps

eaton-general-switch-t0-main-switch-symbol.eps

eaton-rotary-switches-t0-main-switch-symbol.eps

eCAD model

ETN.222867.edz

Installation instructions

IL03801008Z2021_06.pdf

Installation videos

Eaton's P Switch-disconnectors used in a factory

mCAD model

DA-CD-bauform5

DA-CS-bauform5

Product notifications

MZ008006ZU_Orderform_Customized_Switch.pdf

MZ008005ZU_Orderform_Customized_Switch.pdf

Wiring diagrams

eaton-rotary-switches-t0-on-off-switch-wiring-diagram-024.eps

eaton-rotary-switches-t0-on-off-switch-wiring-diagram-023.eps

evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Fitted with:

Red rotary handle and yellow locking ring

Operating frequency

1200 Operations/h

Pollution degree

3

Climatic proofing

Damp heat, constant, to IEC 60068-2-78

Damp heat, cyclic, to IEC 60068-2-30

Rated impulse withstand voltage (Uimp)

6000 V AC

Rated operational power star-delta at 500 V, 50 Hz

18.5 kW

Rated operational power star-delta at 690 V, 50 Hz

22 kW

Rated permanent current at AC-21, 400 V

32 A

Rated permanent current at AC-23, 400 V

32 A

Rated uninterrupted current (I_u)

32 A

Static heat dissipation, non-current-dependent P_{vs}

0 W

Switching angle

90 °

Switching power at 400 V

15 kW

Voltage per contact pair in series

60 V

Rated operational power at AC-3, 500 V, 50 Hz

15 kW

Device construction

Complete device in housing

Rated short-time withstand current (I_{cw})

0.65 kA

650 A, Contacts, 1 second

Electrical connection type of main circuit

Screw connection

Design

15259

Mounting position

As required

Actuator type

Door coupling rotary drive

Ambient operating temperature - max

40 °C

Ambient operating temperature - min

-25 °C

Ambient operating temperature (enclosed) - max

40 °C

Ambient operating temperature (enclosed) - min

-25 °C

Equipment heat dissipation, current-dependent P_{vid}

1.1 W

Heat dissipation capacity P_{diss}

0 W

Heat dissipation per pole, current-dependent P_{vid}

1.1 W

Number of auxiliary contacts (change-over contacts)

0

Number of auxiliary contacts (normally closed contacts)

0

Rated conditional short-circuit current (I_q)

1 kA

Overvoltage category

III

Control circuit reliability

1 failure per 100,000 switching operations statistically
determined, at 24 V DC, 10 mA)

Degree of protection (front side)

IP65

Number of poles

3

Mounting method

Surface mounting

Degree of protection

NEMA 12

Suitable for

Ground mounting

Branch circuits, suitable as motor disconnect, (UL/CSA)

Functions

Emergency switching off function

Interlockable

Number of switches

1

Safe isolation

440 V AC, Between the contacts, According to EN 61140

Screw size

M4, Terminal screw

Shock resistance

12 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms

Lifespan, mechanical

500,000 Operations

Load rating

1.6 x I_e (with intermittent operation class 12, 40 % duty factor)

1.3 x I_e (with intermittent operation class 12, 60 % duty factor)

2 x I_e (with intermittent operation class 12, 25 % duty factor)

Terminal capacity

2 x (0.75 - 4) mm², flexible with ferrules to DIN 46228

1 x (0.75 - 4) mm², flexible with ferrules to DIN 46228

2 x (1 - 6) mm², solid or stranded

1 x (1 - 6) mm², solid or stranded

Safety parameter (EN ISO 13849-1)

B10d values as per EN ISO 13849-1, table C.1

Number of auxiliary contacts (normally open contacts)

2

Number of contact units

3

Number of contacts in series at DC-21A, 240 V

1

Number of contacts in series at DC-23A, 120 V

3

Number of contacts in series at DC-23A, 24 V

1

Number of contacts in series at DC-23A, 240 V

5

Number of contacts in series at DC-23A, 48 V

2

Number of contacts in series at DC-23A, 60 V

3

Rated breaking capacity at 220/230 V (cos phi to IEC 60947-3)

260 A

Rated breaking capacity at 400/415 V (cos phi to IEC 60947-3)

260 A

Rated breaking capacity at 500 V (cos phi to IEC 60947-3)

240 A

Rated breaking capacity at 660/690 V (cos phi to IEC 60947-3)

170 A

Rated making capacity up to 690 V (cos phi to IEC/EN 60947-3)

320 A

Rated operating voltage (Ue) - max

690 V

Rated operating voltage (Ue) - min

690 V

Rated operational voltage (Ue) at AC - max

690 V

Short-circuit protection rating

35 A gG/gL, Fuse, Contacts

Rated operational current (Ie) at AC-21, 440 V

32 A

Rated operational current (Ie) at AC-23A, 230 V

32 A

Rated operational current (Ie) at AC-23A, 400 V, 415 V

32 A

Rated operational current (Ie) at AC-23A, 500 V

26.4 A

Rated operational current (Ie) at AC-23A, 690 V

17 A

Rated operational current (Ie) at AC-3, 220 V, 230 V, 240 V

23.7 A

Rated operational current (Ie) at AC-3, 380 V, 400 V, 415 V

23.7 A

Rated operational current (Ie) at AC-3, 500 V

23.7 A

Rated operational current (Ie) at AC-3, 660 V, 690 V

14.7 A

Rated operational current (Ie) at DC-1, load-break switches I/r = 1 ms

25 A

Rated operational current (Ie) at DC-13, control switches L/R = 50 ms

20 A

Rated operational current (I_e) at DC-21, 240 V

1 A

Rated operational current (I_e) at DC-23A, 120 V

12 A

Rated operational current (I_e) at DC-23A, 24 V

25 A

Rated operational current (I_e) at DC-23A, 240 V

5 A

Rated operational current (I_e) at DC-23A, 48 V

25 A

Rated operational current (I_e) at DC-23A, 60 V

25 A

Rated operational current (I_e) star-delta at AC-3, 220/230 V

32 A

Rated operational current (I_e) star-delta at AC-3, 380/400 V

32 A

Rated operational current (I_e) star-delta at AC-3, 500 V

32 A

Rated operational current (I_e) star-delta at AC-3, 690 V

25.5 A

Rated operational current for specified heat dissipation (I_n)

32 A

Rated operational power at AC-23A, 220/230 V, 50 Hz

7.5 kW

Rated operational power at AC-23A, 400 V, 50 Hz

15 kW

Rated operational power at AC-23A, 500 V, 50 Hz

15 kW

Rated operational power at AC-23A, 690 V, 50 Hz

15 kW

Rated operational power at AC-3, 380/400 V, 50 Hz

11 kW

Rated operational power at AC-3, 415 V, 50 Hz

11 kW

Rated operational power at AC-3, 690 V, 50 Hz

11 kW

Rated operational power star-delta at 220/230 V, 50 Hz

7.5 kW

Rated operational power star-delta at 380/400 V, 50 Hz

15 kW

Tightening torque

1.6 Nm, Screw terminals

Uninterrupted current

Rated uninterrupted current I_u is specified for max. cross-section.



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia