




Connectors > Rectangular Connectors > Rectangular Contact Inserts



Rectangular Connector Insert Type: **Insert for Contacts**

Contact Type: **Socket**

Number of Positions: **23**

Features

Product Type Features

Rectangular Connector Insert Type	Insert for Contacts
-----------------------------------	---------------------

Configuration Features

Number of Positions	23
---------------------	----

Body Features

Primary Product Material	Phenolic
Primary Product Color	Black

Contact Features

Contact Type	Socket
--------------	--------

Packaging Features

Packaging Method	Package
Packaging Quantity	45

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC




Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #CAT-T3437-T548  
TMS-SCE Military Grade Sleeves




TE Part #59239-4  
HHHT PIDG PG 12-10 ASSY




TE Part #878122-000  
207W234-3-01-0




TE Part #66103-1  
III+ PIN,24-20,30AU>10,LP




TE Part #66105-1  
III+ SKT,24-20,30AU>10,LP



TE Part #0641-2-1631L  
CONT PIN



TE Part #6-1393246-7  
W23-X1A1G-2=W23/W31



TE Part #5260010007  
TC-CAPS-4001-9

Documents

Product Drawings  
SKT MODULE, 23 POSN, G-SERIES  
English

CAD Files  
3D PDF  
3D  
Customer View Model  
ENG\_CVM\_CVM\_202651-4\_AA.2d\_dxf.zip  
English  
Customer View Model



ENG\_CVM\_CVM\_202651-4\_AA.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_202651-4\_AA.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

Instruction Sheet (U.S.)

English

AMP 23 POSITION SERIES "G" MODULES FOR AMP TYPE II, III & III PLUS AN

English

Agency Approvals

Agency Approval Document

English