

## Coupling - VS-MP-PPC/CG-PO - 1403681

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Multi-port power connection: push/pull power, for passive PROFINET cabling to robots, including mounting foot.

### Product description

Push/pull data coupling; version 14



### Key commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Packing unit                         | 1 pc                           |
| GTIN                                 | <br>4 046356 664301            |
| Weight per Piece (excluding packing) | 288.3 g                        |
| Custom tariff number                 | 85366990                       |
| Country of origin                    | Germany                        |
| Note                                 | Made to Order (non-returnable) |

### Technical data

#### Mechanical characteristics

|                             |                                   |
|-----------------------------|-----------------------------------|
| Connection profile          | Power: 5-pos.                     |
| Insertion/withdrawal cycles | ≤ 100 (Power)                     |
| Connection method           | Spring-cage connection            |
| Max. cable diameter         | 9 mm ... 13 mm (Data cable gland) |

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -40 °C ... 70 °C |
| Degree of protection            | IP65             |

#### Material data

|                  |  |
|------------------|--|
| Housing material | Aluminum press-drawn section / die-cast zinc |
|------------------|--|

#### Electrical characteristics

|                       |      |
|-----------------------|------|
| Nominal voltage $U_N$ | 24 V |
| Nominal current $I_N$ | 16 A |

# Coupling - VS-MP-PPC/CG-PO - 1403681

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 272607xx |
| eCl@ss 4.1 | 27260701 |
| eCl@ss 5.0 | 27260701 |
| eCl@ss 5.1 | 27061801 |
| eCl@ss 6.0 | 27061801 |
| eCl@ss 7.0 | 27061801 |

### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000830 |
| ETIM 4.0 | EC001134 |
| ETIM 5.0 | EC001134 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 26121616 |
| UNSPSC 7.0901 | 26121616 |
| UNSPSC 11     | 26121604 |
| UNSPSC 12.01  | 31261501 |
| UNSPSC 13.2   | 26121616 |

## Approvals

### Approvals

---

### Approvals

EAC

---

### Ex Approvals

---

### Approvals submitted

---


### Approval details

|     |
|-----|
| EAC |
|-----|

## Drawings

## Coupling - VS-MP-PPC/CG-PO - 1403681

Drilling diagram



Dimensioned drawing

