

## FEATURES

- **Graphite and PTFE material:** Provides excellent chemical resistance and durability
- **Maximum operating pressure of 8500 kPa:** Suitable for high-pressure applications
- **Maximum operating temperature of 280°C:** Ensures reliable performance in high-temperature environments
- **Rotary speed of 28 m/s:** Supports efficient operation in dynamic applications
- **3 mm section:** Allows for precise fitting and sealing

## RS PRO 8m Gland & Valve Packing, Graphite PTFE

RS Stock No: 606-560



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

RS PRO gland and valve packing is designed for high-performance sealing in industrial applications. Made from a combination of graphite and polytetrafluoroethylene, this packing offers excellent durability and resistance to high temperatures and pressures, making it ideal for demanding environments.

## General Specifications

Maximum Operating Pressure	8500 kPa
Product Type	Gland & Valve Packing
Rotary Speed	28 m/s
Section	3 mm
Sub Type	Gland Packing

## Mechanical Specifications

Length	8 m
Material	Graphite, Polytetrafluoroethylene

## Operation Environment Specifications

Maximum Operating Temperature	280 °C
-------------------------------	--------

## Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------