
**RNA4919-XL**

Radial roller bearing

Radial roller bearing RNA..-XL

X-life

Technical information



Your current product variant

Cage	Standard	Standard
Lubrication hole	with	with
Coating	Without	
Sealing	Without	
Special features	Without	
Number of rolling element rows	1	Single-row design

Main Dimensions & Performance Data

F_w	110 mm	Under roller diameter
D	130 mm	Outside diameter
B	35 mm	Width
C_r	131,000 N	Basic dynamic load rating, radial
C_{0r}	260,000 N	Basic static load rating, radial
C_{ur}	45,000 N	Fatigue load limit, radial
n_G	4,200 1/min	Limiting speed
$n_{G \text{ Grease}}$	2,500 1/min	Limiting speed for grease lubrication
n_{gr}	2,500 1/min	Reference speed
$\approx m$	0.718 kg	Weight








Dimensions

r _{min}	1.1 mm	Minimum chamfer dimension
C	35 mm	Width, outer ring

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.

Characteristics

-  Radial load
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Small design envelope