


FEATURES

- **Annealed Copper Conductor:** Offers superior conductivity and flexibility for efficient electrical performance
- **Polyvinyl Chloride Jacket:** Provides robust protection against abrasion and environmental conditions
- **Plain Conductor Type:** Ensures consistent electrical properties and ease of installation
- **24/0.2 Core Strands:** Enhances flexibility and durability, suitable for dynamic applications
- **Operating Temperature Range -15 °C to 70 °C:** Suitable for a wide range of environments
- **Voltage Rating of 500 V:** Supports high voltage applications safely
- **Black Jacket Colour:** Ideal for discrete installations and easy identification

RS PRO 0.75 mm² Flexible Cable, 100 m Length

RS Stock No: 606-060



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible cable is designed for reliable electrical connections in various industrial and commercial applications. With a conductor made from annealed copper, it ensures excellent conductivity and flexibility, making it ideal for installations requiring frequent movement or bending. The cable is insulated with a durable polyvinyl chloride jacket, providing protection against environmental factors.

General Specifications

Conductor Material	Annealed Copper
Conductor Type	Plain
Jacket Colour	Black
Product Type	Flexible Cable

Mechanical Specifications

Cable CSA	0.75 mm ²
Cable Length	100 m
Core Strands	24/0.2
Jacket Material	Polyvinyl Chloride
Number of Cores	2
Outside Diameter	7.2 mm

Operation Environment Specifications

Maximum Operating Temperature	70 °C
Minimum Operating Temperature	-15 °C

Approvals

Standards/Approvals	ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228
---------------------	---

Electrical Specifications

Voltage	500 V
---------	-------